

# **Specification Summary**

NERV Stock - MXP150, 4x4 F450 -North Eastern Rescue Vehicles, Inc

North Eastern Rescue Vehicles Bob Reilly 10 Dwight Park Drive

Syracuse, NY

#### Name

#### Type I - MXP150



### **Specifications**

Overall Length 285" - 291" (724 cm - 739 cm) Overall Width 95" (241 cm) Overall Height 110" (279 cm)\*\* Headroom 72" (183 cm) Wheelbase 165" - 168" (411 cm - 427 cm)\* Payload Capacity Up to 4500 lbs (2041 kg)

# **Sales Options by Category**

### 0-Change Order (CO)

Name/Description

Quantity

## Name/Description

Quantity

KKK

1.00

This specification identifies the minimum requirements for new automotive Emergency Medical Services (EMS) ambulances (except military field ambulances) built on Original Equipment Manufacturer's Chassis (OEM) that are prepared by the OEM for use as an ambulance.



	<b>TYPE I - MXP150</b> TYPE I - MXP150	1.00
	Type I - Pick up Type I - Pick up	1.00
11-Chassis (CH*		
	Name/Description	Quantity
	Conversion Ford F350/F450 Chassis Cab Conversion Ford F350/F450 Chassis Cab Ford F450XLT Super Duty Diesel Chassis Cab 4X4 169 Ford F450XLT Super Duty Diesel Chassis Cab 4X4 1696,7L POWER STROKE V8 Diesel EngineWheelbase 169" (4293 mm)GVWR (Gross vehicle weight rating) 13,300 Lbs / 6,033 Kg	
12-Suspension (	sus)	
	Name/Description	Quantity
13-Module (MO	LiquidSpring™ Suspension Type I  Compressible Liquid Adaptive Suspension System, is a smart suspension systems.  Liquid-based struts and an on-board processor provide better handling and control, and a smoother, softer ride. The reduced vehicle vibration increases comfort.	1.00
19 Module (Mo	Name/Description	Quantity
14-Module Conf	MXP150 Ambulance Module  All Aluminum ambulance module structure, doors structure and accessories.	1.00
,	Name/Description	Quantity
	C1 Door, ALS Access and Battery Location First door on curbside (C1) for ALS compartment access and battery slide out sealed compartment. (Included)	1.00
	C2, Curbside Entry Door, with Opening Window Side entry door on curbside (C2) for patient compartment access, with flush-mounted, automotive-style opening window.	1.00
	C3 Door, Storage Exterior Compartment Third door on curbside (C3) for backboard or other storage. (Included)	1.00
	Empty compartment Compartment without device or divider	1.00
	High-Intensity Compartment Tube Lighting	1.00
	High-intensity tube lighting for Compartments. With Side entry Door Steps.  A1 and A2, Rear Entry Doors, with Defrost  Two (2) rear entry doors for patient compartment access, each with its individual exterior door handle. Includes frameless flush-mounted tinted windows and defrost feature.	1.00
	S1 Door, Main Oxygen Exterior Compartment First door on streetside (S1) for main vertical oxygen cylinder. (Included)	1.00



S2 Door, Storage Exterior Compartment, Electrical	1.00
Second door on streetside (S2) for equipment storage. Upper enclosed ele	ectrical
compartment. MX164/MXP150	
Stair Chair Holder on Compartment Door	1.00
Stair chair holder on S2 compartment door.	
Fire Extinguisher, ABC-Rated, 5 lbs, with Bracket	1.00
Fire extinguisher, 5 lbs, ABC-rated, with heavy duty bracket in S2 comparts	
Half-Depth Shelf, One (1), Adjustable	1.00
One (1) half-depth, adjustable shelf in S2 compartment.	
Full-Depth Shelves, Two (2), Adjustable	1.00
Two (2) full-depth, adjustable shelves in S3 compartment.	
S3 Compartment, Equipment Storage, Short	1.00
Third door on streetside (S3) short for equipment storage.	
15-Lighting (LGT)	
Name/Description	Quantity
Turn Signal Lights, Amber (2), LED	1.00
Two (2) amber turn-signal lights, intermediate side mount. Whelen 700 se	ries (7 x 3)
LED lights.	
Third Upper Brake Light, LED	1.00
Third upper brake light at rear of module. Whelen 600 series (6 x 4) LED light	ght.
Rear Step Plate: Turn Signal Light, Brake, Reverse	1.00
Two (2) red brake/tail lights, two (2) amber turn lights, and two (2) reverse	e lights
installed in rear step plate. Round LED lights.	
Mid-Height Lights: Arrow, Brake, Reverse	1.00
Two (2) amber arrows, two (2) red brake lights, and two (2) reverse lights	at mid
height. Whelen 600 series LED lights (6 x 4).	
Marker Lights, Amber (7) and Red (7), LED	1.00
Seven (7) front upper center and corner amber LED marker lights. Seven (7	') rear upper
center and corner red LED marker lights.	
16-Emergency and Working Lights (EWL)	
Name/Description	Quantity
Clear Lenses	1.00
Clear lenses.	
Chrome bezels	29.00
Chrome bezels	_5,55
Emergency Lights, Red (2), LED, Upper Corners	1.00
Two (2) red lights at upper corners of front face. Whelen 900 series (7 x 9)	
Demers Aerodynamic Cabriser	1.00
Demers aerodynamic cabriser, with a total of twelve (12) lights: four (4) or	
and four (4) at the front. The front lights are a combination of red (1), clea	
with a clear lens. The sides each include four (4) red lights, with a red lens.	
Whelen 500 series, LED.	Č
Lights in Front Grille, Red (2), LED 500	1.00
Two (2) red lights in front grille. Whelen 500 series (5 x 1) LED lights.	
Emergency Lights on Inside of Doors, One (1) each	1.00
One red emergency light on each compartment and entry door inside pan	
eight (8) round LED lights.	
Intersection Lights, Clear/Red (2), LED	1.00
- · · · · · · · · · · · · · · · · · · ·	
Two (2) clear/red intersection lights with turning priority. Whelen 700 seri	les ( / x 3) LED
Two (2) clear/red intersection lights with turning priority. Whelen 700 seri	les (7 x 3) LED
	es (/ x 3) LED



	Two (2) red emergency lights, intermediate side mount. Whelen 700 series (7 x 3) LED	
	lights.	
	Four (4) red LED lateral emergency lights (900)	1.00
	Four (4) red lateral emergency lights (two (2) on each side). Whelen 900 series (7 x 9)	1.00
	LED lights.	
	Scene Lights, Four (4), Clear LED, (900)	1.00
	Four (4) lateral scene lights (two (2) on each side). Whelen 900 series (7 X 9) LED scene	
	lights.	
	Emergency Lights, Red (2), LED, Rear Corners	1.00
	Two (2) red rear emergency lights at upper rear corners. Whelen 900 series (7 x 9) LED	
	lights.	
	Emergency Lights, Amber (2), LED	1.00
	Two (2) rear upper amber lights. Whelen 600 series (6 x 4) LED lights.	4.00
	Loading Lights, Two (2), LED	1.00
	Two (2) rear loading lights. Whelen 600 series (6 x 4) LED lights.	4.00
	Emergency Lights, Red (2), LED, Addt'l, Window Hgt	1.00
47 4 - 111 - 141 - 1	Two (2) additionnal red lights at window height. Whelen 900 series (7 x 9) LED lights.	
17-Audible War	ning System (WRN)	
	Name/Description	Quantity
	Back-Up Alarm	1.00
	Back up alarm (97dB) with override switch.	
	Whelen 295SLS Hands-Free Siren	1.00
	Whelen model 295HFSA1 siren amplifier with 17 Scan-Lock™ siren tones.	
	Switch to Mute OEM Horn when Siren Speakers Active	1.00
	Switch to mute the OEM horn when the siren speakers are activated.	4.00
	Whelen SA315 Series Speakers	1.00
	Whelen SA315 series speakers is a compact speaker meeting SAE Class A requirements	
	when paired with Whelen 100 watt siren amplifier.	1.00
	Backup use OEM Only Backup camera connected to OEM // Patient compartment camera connected to	1.00
	5 inch display monitorRN Backup & patient compartment cameras display in FORD	
	OEM Display.	
18-Exterior Vehi	icle features (VFT)	
	Name/Description	Quantity
	rvanie, Bescription	
	Chrome wheel simulator	
	Chrome wheel simulator Chrome wheel simulator	1.00
	Chrome wheel simulator	1.00
	Chrome wheel simulator Quarter-Tank Fuel Fill	
	Chrome wheel simulator	1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.	1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors	1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors	1.00 1.00 1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors  Module Rub Rails, Aluminum	1.00 1.00 1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors  Module Rub Rails, Aluminum  Aluminium rub rails on module sides.	1.00 1.00 1.00 1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors  Module Rub Rails, Aluminum  Aluminium rub rails on module sides.  Module Corner Protectors, Stainless-Steel	1.00 1.00 1.00 1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors  Module Rub Rails, Aluminum  Aluminium rub rails on module sides.  Module Corner Protectors, Stainless-Steel  Stainless-steel protectors on module corners.  Module Wheel Trims, Fiberglass  Formed fiberglass wheel trimming on module.	1.00 1.00 1.00 1.00 1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors  Module Rub Rails, Aluminum  Aluminium rub rails on module sides.  Module Corner Protectors, Stainless-Steel  Stainless-steel protectors on module corners.  Module Wheel Trims, Fiberglass  Formed fiberglass wheel trimming on module.  Undercoating Protection	1.00 1.00 1.00 1.00 1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors  Module Rub Rails, Aluminum  Aluminium rub rails on module sides.  Module Corner Protectors, Stainless-Steel  Stainless-steel protectors on module corners.  Module Wheel Trims, Fiberglass  Formed fiberglass wheel trimming on module.  Undercoating Protection  Undercoating protection for module and chassis.	1.00 1.00 1.00 1.00 1.00 1.00
	Chrome wheel simulator  Quarter-Tank Fuel Fill  Quarter-tank fuel fill.  OEM exterior mirrors  Keep OEM exterior mirrors  Module Rub Rails, Aluminum  Aluminium rub rails on module sides.  Module Corner Protectors, Stainless-Steel  Stainless-steel protectors on module corners.  Module Wheel Trims, Fiberglass  Formed fiberglass wheel trimming on module.  Undercoating Protection	1.00 1.00 1.00 1.00 1.00



	Chrome License Plate with Light	1.00
	Recessed chrome license plate holder with LED light.	
	Cab Steps, Anti-Skid Material with Mud Guards	1.00
	Anti-skid lateral steps. Includes mud guards for front wheels.	
	Rear Step Bumper, Retractable Center Section	1.00
	Anti-skid rear retractable step. Diamond plate corner bumper. Rubber bumperette.	
19-Convenience	(CNV)	
	Name/Description	Quantity
	Valet Switch in Front Grille	1.00
	The door unlock valet switch is located on the back of the front grille, on the driver's	
	side half portionof the grille. It allows to unlock all doors of the vehicle, but cannot lock	
	the doors.	
	Demers Fast Idle	1.00
	Demers fast idle is generated by the multiplex module, it allows fast charging of the	1.00
	batteries by the engine when specific conditions are met.	
	Black Back-Up Camera	1.00
	RearView Safety standard back-up camera with build-in audio support and infra-red	
	night vision.	
	Black Dome Interior Camera	1.00
	RearView Safety dome interior camera with build-in audio support and 130 degree	
	viewing angle.	
	Anti-Theft System	1.00
	The anti-theft allows leaving the vehicle without keys and the engine running to keep	
	the vehicle at the ideal operating temperature. It protects against theft by turning off	
	the engine if the vehicle moves.	
	ECOSMART Anti-Idling System	1.00
	The ECOSMART Anti-Idling System automatically stops and restarts the engine of the	
	vehicle in idling conditions. The ECOSMART Anti-Idling System is managed by the	
	Demers Electronic MultiplexSystem (DEMS).	
21-Paint and De		
	Name/Description	Quantity
	Tri-Star Urethane Paint	1.00
	Two (2) coats of primer with two (2) coats of urethane. All four (4) sides and roof. No	1.00
	sanding. No buffing.	1.00
	Emblems and Markings	1.00
	"Star of Life" (3", 12", 16" and 32"), "AMBULANCE" (3), and mirrored "AMBULANCE"	
	(1).	
22-Drivers Comp	partment (CAB)	
	Name/Description	Quantity
	Floor-Mounted Console with control	1.00
	Floor-mounted console in front cab.	4.00
	Storage for Flare and Fire Extinguisher	1.00
	Storage compartment in front cab for flares and one (1) five-pound (5 lbs) fire	
	extinguisher.	
	Armrests, Driver and Passenger, Individual	1.00
	Individual driver- and passenger-side armrests on sides of floor-mounted console.	



Cup Holders, Dual, in Floor-Mounted Console	1.00
Dual cup holders in floor-mounted console.	
Control Center with Switches and Touch Pad	1.00
Control center with switches and LED backlit pictograms in the floor mounted console.	
Cab headliner with Reading Lights, Red/Clear (2)	1.00
Two (2) clear and red overhead LED reading lights.	
23-Curbside Configuration (CRB)	
Name/Description	Quantity
Removable "A"-bar with sharps and trash.	1.00
Removable "A"-bar mounted at the front end of the squad bench with sharps and	
trash.	
Full-Length Seat Cushion	1.00
Full-length, thermoformed, molded seat cushion.	
Seat Backrest	2.00
Individual, thermoformed, molded backrests.	
Seating, Two (2) Passengers, 6Pts Safety Belts	1.00
Seating for two (2) passengers with 6-point safety belts.	
24-Streetside Configuration (STR)	
Name/Description	Quantity
Flip-Up Door, Clear Self Latching Sliding Windows	3.00
Aluminum flip-up frames, self-latching for easy restocking of cabinets. Polycarbonate	3.00
clear self latching sliding windows.	
Medical Cabinet, CPR Bench Seat	1.00
Medical cabinet with CPR bench seat.	1.00
CPR Seat , 6-Pt Safety Belt	1.00
·	1.00
Seating for one EMT with 6-point safety peit.	
Seating for one EMT with 6-point safety belt.  25-Forward Bulkhead (FWB)	
25-Forward Bulkhead (FWB)	Quantity
25-Forward Bulkhead (FWB)  Name/Description	Quantity
25-Forward Bulkhead (FWB)  Name/Description Sliding Window Pass-Through	Quantity 1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab.	1.00
25-Forward Bulkhead (FWB)  Name/Description Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment	
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through  Pass-through sliding window on front division for communication with cab.  Locking Radio Communication Compartment  Lockable compartment on street side for radio communication	1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer	1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with	1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through  Pass-through sliding window on front division for communication with cab.  Locking Radio Communication Compartment  Lockable compartment on street side for radio communication  ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip	1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through  Pass-through sliding window on front division for communication with cab.  Locking Radio Communication Compartment  Lockable compartment on street side for radio communication  ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door.	1.00 1.00 1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab.  Locking Radio Communication Compartment Lockable compartment on street side for radio communication  ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door.  Compartment above ALS Cabinet, Lockable	1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door. Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet.	1.00 1.00 1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door.  Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles	1.00 1.00 1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door.  Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet.  See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles	1.00 1.00 1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door. Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles	1.00 1.00 1.00 1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door.  Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles  26-Attendant Seat (AST)  Name/Description	1.00 1.00 1.00 1.00 Quantity
Name/Description Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door. Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles  26-Attendant Seat (AST)  Name/Description EVS Swivel Seat Base, Two (2) Positions	1.00 1.00 1.00 1.00
25-Forward Bulkhead (FWB)  Name/Description Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door. Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles  26-Attendant Seat (AST)  Name/Description EVS Swivel Seat Base, Two (2) Positions EVS swivel 360 degrees seat base, locking in two (2) positions, forward and rearward	1.00 1.00 1.00 1.00 Quantity
25-Forward Bulkhead (FWB)  Name/Description Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door. Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles  26-Attendant Seat (AST)  Name/Description EVS Swivel Seat Base, Two (2) Positions EVS swivel 360 degrees seat base, locking in two (2) positions, forward and rearward positions	1.00 1.00 1.00 1.00  1.00  Quantity 1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door.  Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles  26-Attendant Seat (AST)  Name/Description  EVS Swivel Seat Base, Two (2) Positions EVS swivel 360 degrees seat base, locking in two (2) positions, forward and rearward positions EVS 1880 3Pts Vac-Formed Seamless Child Seat	1.00 1.00 1.00 1.00 Quantity
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door. Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles  26-Attendant Seat (AST)  Name/Description EVS Swivel Seat Base, Two (2) Positions EVS swivel 360 degrees seat base, locking in two (2) positions, forward and rearward positions EVS 1880 3Pts Vac-Formed Seamless Child Seat The EVS 1880 is a vac-form, seamless ambulance attendant's seat. Integrated child	1.00 1.00 1.00 1.00  1.00  1.00  1.00
25-Forward Bulkhead (FWB)  Name/Description  Sliding Window Pass-Through Pass-through sliding window on front division for communication with cab. Locking Radio Communication Compartment Lockable compartment on street side for radio communication ALS Cabinet, without Drawer  ALS cabinet on curbside of front wall. Includes four (4) aluminum extruded doors with see-through windows, adjustable shelve(s), one (1) fixed shelf at mid-height, LED strip lighting, and inside/outside access via curbside door.  Compartment above ALS Cabinet, Lockable Lockable compartment located above the front wall ALS cabinet. See-Through Door, Two Handles Four (4) extruded doors with see through windows and handles  26-Attendant Seat (AST)  Name/Description  EVS Swivel Seat Base, Two (2) Positions EVS swivel 360 degrees seat base, locking in two (2) positions, forward and rearward positions EVS 1880 3Pts Vac-Formed Seamless Child Seat	1.00 1.00 1.00 1.00  1.00  1.00  1.00



	be folded into the seat and allow an adult to use the seat as a standard attendant's seat	
27-Cot Configur		
	Name/Description	Quantity
	Floor Plate & Pre-wire Power-LOAD - GEN 2 (NEW)	1.00
	Stryker Power-Load floor plate. No cot fastener included. Include pre-wiring for	
	charging feature. Default option for new Power-LOAD system from the field.	
	Center Floor-Mount Cot Configuration	1.00
20 Danu Cantual	Center floor mount cot configuration	
28-Rear Control		
	Name/Description	Quantity
	Rocker Switch Controls with LED Backlit Pictograms	1.00
	Auxiliary Rocker switch controls with LED backlit pictograms.	1.00
	Rocker Switch Controls with LED Backlit Pictograms  Rocker switch controls with LED backlit pictograms.	1.00
29-Oxygen (OXY		
29-Oxygen (OX)		Ougustitus
	Name/Description	Quantity
	Oxygen Outlets, Four (4) Four (4) oxygen outlets. Two (2) in ECC, one (1) on curbside, and one (1) on the ceiling.	1.00
	Oxygen Outlet, Quick-Connect	4.00
	Quick-connect style oxygen outlet.	4.00
	Oxygen Regulator, Manual, Sensor and Dig. Read-Out	1.00
	Manual oxygen regulator with pressure sensor and digital read-out.	
	Oxygen Control Valve, Electronic, Manual By-Pass	1.00
	Electronic oxygen control valve with manual by-pass.	
	Storage for Two (2) "D-Size" Portable Cylinders	1.00
	"D-size" Portable oxygen cylinder storage (2), located in side entry door.	
	Universal Vertical Holder for Main Oxygen Cylinder	1.00
	Universal vertical holder for types "K" or "M" main oxygen cylinder in S1 streetside exterior compartment.	
31-Suction (SUC	•	
31-3uction (30C		0
	Name/Description	Quantity
	Suction System location in ECC  Main suction system is located in front streetside action area.	1.00
	Thomas high flow vacuum pump	1.00
	Thomas high flow vacuum pump	1.00
	Vacuum outlet QD in action area	1.00
	Vacuum outlet QD Puritan with yellow 5/16" hose 4 ft long	
	Vacuum regulator with disposable canister	1.00
	Vacuum regulator with disposable canister	
32-Electrical Sys	tem (ELE)	
	Name/Description	Quantity
	Power Inverter, Xantrex Freedom, True Sine, 1000W	1.00
	The inverter/charger provides AC power using the DC power from the conversion	
	battery bank. Recharge all battery banks and power all 120 volts AC outlets when the	
	external shoreline is connected.	
	Super Auto Eject Power Inlet, 20 Amps, Yellow	1.00
	Kusmaull 120 Volts AC, 20 Amps - Automatically disconnects shoreline - Completely	
	sealed - Yellow cover - Indicator light.	



	Electrical Outlet, 120V AC with Indicator	1.00
	120V AC hospital-grade electrical outlets with indicator.	
	ACDelco Conversion Batteries	1.00
	Two (2) ACDelco conversion Batteries.	1.00
	Electrical Outlet, 12V DC 20 amp with Indicator  12V DC, 20 amp Duplex electrical outlets.	1.00
	Add Dual USB DC outlet with indicator	1.00
	Additional dual USB DC outlet with indicator. Details and location are as follows: (1) in	1.00
	Action Area (ECC); (1) in cab console	
	Demers Multiplex Electronic Management System	1.00
	Demers Electronic Management System (DEMS) – Multiplex system.	
33-Communica	tion System (COM)	
	Name/Description	Quantity
	Pre-Wiring for 2-Way Radio, Two (2) Antenna Cables	1.00
	Wiring preparation for two-way radio, with two (2) antenna cables.(routed from front	
	cab to radio communication compartment)	
	Radio Communications Compartment	1.00
	Radio communications compartment universal board, Bussmann blade-type fuse	
	panels, and harness to power the radio communication devices.(12V battery feed,	
	ground, ignition).	
	Radio Communications Front Console	1.00
	Radio communications front console universal board, Bussmann blade-type fuse	
	panels, and harness.	
	Data Recorder Available Signals	1.00
	Data recorder available signals through a universal connector in the electrical	
	compartment.	
24 HVAC (CVC)		
34-HVAC (CVC)		0
34-HVAC (CVC)	Name/Description	Quantity
34-HVAC (CVC)	Name/Description Dual condenser 135000 BTU, Roof LP	Quantity 1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU	1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU  Independent Air Conditioning System	
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU  Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the	1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU  Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.	1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU  Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round	1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.	1.00 1.00 1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU  Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit	1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU  Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient	1.00 1.00 1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets. Air Conditioning Outlets, Round Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor	1.00 1.00 1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU  Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.	1.00 1.00 1.00 1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)	1.00 1.00 1.00
34-HVAC (CVC)	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear	1.00 1.00 1.00
	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear console switch.	1.00 1.00 1.00
34-HVAC (CVC)  35-Interior Ligh	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear console switch.	1.00 1.00 1.00 1.00
	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear console switch.  Its (ILG)  Name/Description	1.00 1.00 1.00 1.00 Quantity
	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear console switch.  Its (ILG)  Name/Description  LED Dome Lights, Adjustable, Dig. Timer	1.00 1.00 1.00 1.00
	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear console switch.  Its (ILG)  Name/Description  LED Dome Lights, Adjustable, Dig. Timer  The ceiling lights have four (4) different intensities. Each time the ceiling lights button	1.00 1.00 1.00 1.00 Quantity
35-Interior Ligh	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear console switch.  Its (ILG)  Name/Description  LED Dome Lights, Adjustable, Dig. Timer  The ceiling lights have four (4) different intensities. Each time the ceiling lights button is pushed, the intensity increases, until maximum intensity is reached.	1.00 1.00 1.00 1.00 Quantity
	Name/Description  Dual condenser 135000 BTU, Roof LP  Auxiliary dual condenser low profile roof mounted - ACC Climate Control 135000 BTU Independent Air Conditioning System  The compressor, condenser and evaporator form an assembly independent of the OEM, cooling the air of the patient compartment through the ducted outlets.  Air Conditioning Outlets, Round  Round outlets for ducted air conditioning unit.  OEM Tie-In Heating Unit  The heating system is an extension of the OEM heating system, heating the patient compartment area through invisible opening underneath the medical cabinet at floor level.  Exhaust Fans (2)  Two (2) exhaust fans for contaminated air. Activated by front control interface or rear console switch.  Its (ILG)  Name/Description  LED Dome Lights, Adjustable, Dig. Timer  The ceiling lights have four (4) different intensities. Each time the ceiling lights button is pushed, the intensity increases, until maximum intensity is reached.	1.00 1.00 1.00 1.00 2.00



Grab Bars Color, Vellow Color of selected grab bars is Yellow. Rear Door-Mounted Grab Bars, 16" x 16" Two (2) door-mounted grab bars, 16" x 16" x 16" Curbside Door-Mounted Grab Bars, 12" One (1) door-mounted grab bar, 12" each, on the inside of the side entry door (C2). (included) Embarking Grab Bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door. Ceiling Grab Rails, 90", Two (2) Two (2) ceiling-mounted grab lail, 90". Two (2) ceiling-mounted grab lail, 90".  37-Finish and Trim (FNS)  Name/Description  Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Clobalt blue vinyl upholstery for safety exit padding covering. Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling All patient compartment upholstery Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers (Included) Venote general labels identification Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Curbside Sox Geompartment and Glove Box Holders Combo Storage Compartment and Glove Box Holders			
Rear Door-Mounted Grab Bars, 16" x 16" Two (2) door-mounted grab bars, 16" x 16", inside of rear doors (A1 and A2). Curbside Door-Mounted Grab Bars, 12" One (1) door-mounted grab bar, 12" each, on the inside of the side entry door (C2). (included) Embarking Grab Bars, 12" Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door. Celling Grab Rails, 90", Two (2) Two (2) celling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description  Quantity Lonseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery Yellow winyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass ceiling Fiberglass ceiling in Patient Compartment. General Vehicle Identification Vehicle general labels Identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor Pd43TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor Combo Storage Compartment and Celling, Flexible, Four (4) Four (4) recessed flexible IV hooks in celling. Combo Storage Campartment and Glove Box Holders Combo Storage capinet with LED strip lighting and sliding doors, and glove box compartment or three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash container Flip-Down, Hands-Free Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)		Grab Bars Color, Yellow	1.00
Two (2) door-mounted grab bars, 16" x 15", inside of rear doors (A1 and A2).  Curbside Door-Mounted Grab Bar, 12" One (1) door-mounted grab bar, 12" each, on the inside of the side entry door (C2). (included) Embarking Grab Bars, 12" Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door.  Celling Grab Rails, 90", Two (2) Two (2) celling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description  Quantity Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Collbalt blue vinyl upholstery for seat and padding covering. Safety Vellow Upholstery Yellow vinyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Celling Fiberglass Fiberglass Celling Fiberglass Fiberglass Fiberglass Fiberglass Fibe			
Curbside Door-Mounted Grab Bar, 12" One (1) door-mounted grab bar, 12" each, on the inside of the side entry door (C2). (included) Embarking Grab Bars, 12" Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door. Celling Grab Rails, 99, "Two (2) Two (2) celling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description Voisseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Celling in Patient Compartment. General Vehicle Identification Vehicle general labels identification.  1.00 Vehicle general Celling, Flexible, Four (4) Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor Covering P443TXM Midnight Lon Plate II Floor (4) recessed radio speakers, (included) IV Hooks, Recessed in Celling, Flexible, Four (4) Four (4) recessed flexible IV hooks in celling. Combo Storage compartment and Glove Box Holders Combo Storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash container bracket in curbside flip-down container. Digital Clock, priver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding a			1.00
One (1) door-mounted grab bar, 12" each, on the inside of the side entry door (C2). (included)  Embarking Grab Bars, 12"  Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door.  Ceiling Grab Rails, 90", Two (2)  Two (2) ceiling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description  Name/Description  Quantity  Lonseal, Lonplate II, Gun Metal floor covering.  Cobalt Blue Upholstery  Colbalt blue vinyl upholstery for seat and padding covering.  Safety Yellow Upholstery  Yellow vinyl upholstery for safety exit padding covering.  Safety Yellow Upholstery for safety exit padding covering.  Wood Flooring  Exterior grade plywood, 0,75 inches thick.  Fiberglass Ceiling in Patient Compartment.  General Vehicle Identification.  Black Upholstery  All patient compartment upholstery and seats BLACK except YELLOW head pads floor P443TXM Midnight Lon Plate II  Floor covering P443TXM Midnight Lon Plate II  1.00  Two (2) recessed radio speakers (Included)  IV Hooks, Recessed in Ceiling, Flexible, Four (4)  Four (4) recessed fields peakers (Included)  IV Hooks, Recessed in Ceiling, Flexible, Four (4)  Four (4) recessed and Glove Box Holders  Combo Storage Compartment and Glove Box Holders  Trash Container, Flip-Down, Hands-Free  Trash container pracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights  Digital clock, rear step Indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description  Name/Description  Loundity  Curbside 2pts Squad Bench Exception  Exception (EXC)			
(included) Embarking Grab Bars, 12" Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door. Ceiling Grab Rails, 90", Two (2) Two (2) ceiling-mounted grab rails, 90".  37-Finish and Trim (FNS)    Name/Description			1.00
Embarking Grab Bars, 12" Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door.  Ceiling Grab Rails, 90", Two (2) Two (2) ceiling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description Quantity Lonseal, Lonplate II, Gun Metal Conseal, Lonplate II, Gun Metal Gor covering. Cobalt Blue Upholstery Cobalt Blue Upholstery or seat and padding covering. Safety Yellow Upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling in Patient Compartment. General Vehicle Identification. Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM in ceiling. Combo Storage Compartment and Glove Box Holders Trash Container, Flip-Down, Hands-Free Digital Clock, priver and Step Indicator Lights Digital Clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)			
Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the R2 rear entry door. Ceiling Grab Rails, 90", Two (2) Two (2) ceiling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description Quantity Lonseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling in Patient Compartment. General Vehicle Identification Place general labels identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Server covering P443TXM Midnight Lon Plate II Combo Storage Compartment and Glove Box Holders Combo Storage Compartment and Glove Box Holders Combo Storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash Container, Flip-Down, Hands-Free Digital Clock, priver and Step Indicator Lights Digital clock, ear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Located in padding above the rear doors.			
near the curbside entry door, and one (1) near the R2 rear entry door.  Ceiling Grab Rails, 90", Two (2)  Two (2) ceiling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description  Lonseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering.  Safety Yellow Upholstery for safety exit padding covering.  Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling in Patient Compartment. General Vehicle Identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Combo Storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free Trash container, Flip-Down, Hands-Free Trash container practed in cybic flight, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1.00
Ceiling Grab Rails, 90", Two (2) Two (2) ceiling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description Quantity Lonseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling in Patient Compartment. General Vehicel Identification Fiberglass Ceiling in Patient Compartment. General Vehicel Identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Quantity Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers. (Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage Compartment of these (3) boxes. Trash Container, Flip-Down, Hands-Free Trash container bracket in curbside flip-down container. Digital Clock, rear step indicator light, driver intention indicator lights (direction, bracker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Lunck (EXC)  Rune/Description Carboid Pate Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compar			
Two (2) ceiling-mounted grab rails, 90".  37-Finish and Trim (FNS)  Name/Description  Lonseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering.  Cobalt Blue Upholstery Cobalt blue vinyl upholstery for seat and padding covering.  Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering.  Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling in Patient Compartment.  General Vehicle Identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Quantity Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers, (Included) IV Hooks, Recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage Compartment of Ceiling, Flexible, Four (4) Trash Container, Flip-Down, Hands-Free Trash Container, Flip-Down, Hands-Free Trash Container bracket in curbside flip-down container. Digital Clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Lucuside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			
Name/Description   Quantity			1.00
Name/Description  Lonseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Ceiling in Patient Compartment. General Vehicle Identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P43TXM Midnight Lon Plate II Floor covering P43TXM Midnight Lon Plate II Floor covering P43TXM Midnight Lon Plate II Compartment upholstery and seate State			
Lonseal, Lonplate II, Gun metal Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Ceiling in Patient Compartment. General Vehicle Identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Sa8-Functionality (FCT)  Name/Description Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers, (Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage Compartment and Glove Box Holders Combo Storage Compartment and Glove Box Holders Trash Container, Flip-Down, Hands-Free Trash Container, Flip-Down, Hands-Free Trash Container, Flip-Down, Hands-Free Trash Container, Flip-Own, Hands-Free Trash container steep indicator light, dirver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating	37-Finish and Tr	rim (FNS)	
Lonseal, Lonplate II, Gun Metal floor covering. Cobalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling F		Name/Description	Quantity
Cobalt Blue Upholstery Colbalt blue vinyl upholstery for seat and padding covering. Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering. Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Ceiling Fiberglass ceiling in Patient Compartment. General Vehicle Identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  338-Functionality (FCT)  Name/Description Quantity Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers, (Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, priver and Step Indicator Lights Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		Lonseal, Lonplate II, Gun metal	1.00
Colbalt blue vinyl upholstery for seat and padding covering.  Safety Yellow Upholstery for safety exit padding covering.  Wood Flooring 1.00 Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling 1.00 Fiberglass Ceiling in Patient Compartment.  General Vehicle Identification 1.00 Vehicle general labels identification. Black Upholstery 1.00 All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TKM Midnight Lon Plate II 1.00 Floor covering P443TXM Midnight Lon Plate II 1.00 Floor (2) recessed radio speakers, (Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (2) recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage Compartment and Glove Box Holders Combo Storage Compartment and Glove Box Holders Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital Clock, priver and Step Indicator Lights, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		Lonseal, Lonplate II, Gun Metal floor covering.	
Safety Yellow Upholstery Yellow vinyl upholstery for safety exit padding covering.  Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Ceiling in Patient Compartment. General Vehicle Identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  7 Wod2) recessed radio speakers, (Included) IV Hooks, Recessed, Two (2) Four (4) recessed radio speakers, (Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights 1.00 Digital clock, rear step indicator Lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1.00
Yellow vinyl upholstery for safety exit padding covering.  Wood Flooring Exterior grade plywood, 0,75 inches thick. Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling Fiberglass Ceiling in Patient Compartment.  General Vehicle Identification.  Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Quantity Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers, (Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash Container bracket in curbside flip-down container. Digital Clock, Priver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		Colbalt blue vinyl upholstery for seat and padding covering.	
Wood Flooring   1.00		Safety Yellow Upholstery	1.00
Wood Flooring   1.00		Yellow vinyl upholstery for safety exit padding covering.	
Fiberglass Ceiling Fiberglass Ceiling Fiberglass ceiling in Patient Compartment.  General Vehicle Identification Vehicle general labels identification.  Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Quantity Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1.00
Fiberglass Ceiling Fiberglass Ceiling Fiberglass ceiling in Patient Compartment.  General Vehicle Identification Vehicle general labels identification.  Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Quantity Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			
Fiberglass ceiling in Patient Compartment.  General Vehicle Identification Vehicle general labels identification.  Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, car step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1.00
General Vehicle Identification Vehicle general labels identification. Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage Campartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free 1.00 Trash container, Flip-Down, Hands-Free Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			
Vehicle general labels identification.  Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1.00
Black Upholstery All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II 1.00 Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash container, Flip-Down, Hands-Free Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		Vehicle general labels identification.	
All patient compartment upholstery and seats BLACK except YELLOW head pads Floor P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description  Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo Storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1.00
Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			
Floor covering P443TXM Midnight Lon Plate II  38-Functionality (FCT)  Name/Description Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		Floor P443TXM Midnight Lon Plate II	1.00
Name/Description  Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		Floor covering P443TXM Midnight Lon Plate II	
Name/Description  Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating	38-Functionality	(FCT)	
Radio Speakers, Recessed, Two (2) Two (2) recessed radio speakers.(Included) IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			Quantity
Two (2) recessed radio speakers.(Included)  IV Hooks, Recessed in Ceiling, Flexible, Four (4)  Four (4) recessed flexible IV hooks in ceiling.  Combo Storage Compartment and Glove Box Holders  Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free  1.00  Trash container bracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights  Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description  Quantity  Curbside 2pts Squad Bench Exception  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		· · · · · ·	
IV Hooks, Recessed in Ceiling, Flexible, Four (4) Four (4) recessed flexible IV hooks in ceiling. Combo Storage Compartment and Glove Box Holders Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes. Trash Container, Flip-Down, Hands-Free Trash container bracket in curbside flip-down container. Digital Clock, Driver and Step Indicator Lights Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  ### Observation (EXC)    Name/Description			2.00
Four (4) recessed flexible IV hooks in ceiling.  Combo Storage Compartment and Glove Box Holders  Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free  Trash container bracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights  Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  **O5-Exception (EXC)**  Name/Description  Quantity  Curbside 2pts Squad Bench Exception  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1 00
Combo Storage Compartment and Glove Box Holders  Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free  Trash container bracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights  Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  D5-Exception (EXC)  Name/Description  Quantity  Curbside 2pts Squad Bench Exception  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			
Combo storage cabinet with LED strip lighting and sliding doors, and glove box compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights 1.00 Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception 1.00 Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1 00
compartment for three (3) boxes.  Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights 1.00 Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception 1.00 Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			2.00
Trash Container, Flip-Down, Hands-Free 1.00 Trash container bracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights 1.00 Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity Curbside 2pts Squad Bench Exception 1.00 Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			
Trash container bracket in curbside flip-down container.  Digital Clock, Driver and Step Indicator Lights  Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description  Curbside 2pts Squad Bench Exception  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		•	1.00
Digital Clock, Driver and Step Indicator Lights  Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description  Curbside 2pts Squad Bench Exception  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		·	2.00
Digital clock, rear step indicator light, driver intention indicator lights (direction, braker) located in padding above the rear doors.  **O5-Exception (EXC)**  **Name/Description**  **Curbside 2pts Squad Bench Exception**  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating**			1 00
braker) located in padding above the rear doors.  05-Exception (EXC)  Name/Description Quantity  Curbside 2pts Squad Bench Exception 1.00  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			1.30
05-Exception (EXC)Name/DescriptionQuantityCurbside 2pts Squad Bench Exception1.00Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating			
Name/Description  Curbside 2pts Squad Bench Exception  Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating	05-Exception (F.		
Curbside 2pts Squad Bench Exception 1.00 Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating	35 ZACCPCION (E)	·	Quantity
Exception taken to KKK 3.11.4 or CAAS C.12.4 Patient Compartment Seating		· · · · · · · · · · · · · · · · · · ·	
			1.00
Snarps Container inside Module Exception 1.00			1.00
		Sharps Container inside Module exception	1.00



Exception taken to KKK 3.11.1.2 CAAS C 12.1.2 Waste and Sharps Disposal - No Sharps container selected