

Purchaser: North Eastern Rescue Vehicles
Contact: Bob Reilly
Address: 10 Dwight Park Drive
 Syracuse, NY

North Eastern Rescue Vehicles, Inc.

Phone: (315) 414-9999

Name

CCL150



Specifications

- Aluminum Extruded Body Construction
- CrestCoat Powder Coating Technology
- Aluminum Cabinets
- Multiplex Electrical System
- Flush Mount Windows

Sales Options by Category

Base

| Name/Description | Quantity |
|---|----------|
| TYPE I - CCLP150 | 1.00 |
| TYPE I - CCLP150 | |
| 72in Interior Headroom | 1.00 |
| 72in Interior Headroom | |
| KKK-A-1822F | 1.00 |
| KKK-A-1822F - USA Government Federal Specification for a Star-of-Life Ambulance | |

Chassis

| Name/Description | Quantity |
|------------------|----------|
|------------------|----------|

| | |
|--|------|
| Ford F350 chassis cab 4x4 diesel | 1.00 |
| Ford F350XL Super Duty Diesel Chassis Cab 4X4 1696,7L POWER STROKE V8 Diesel Engine/Wheelbase 169" (4293 mm)GVWR (Gross vehicle weight rating) 13,300 Lbs / 6,033 Kg | |
| Anti-theft | 1.00 |
| Anti-theft security system | |
| High Idle | 1.00 |
| High Idle system | |
| OEM chassis mirrors | 1.00 |
| OEM chassis mirrors | |
| Wheel alignment | 1.00 |
| Wheel alignment completed at the factory | |
| Running Boards | 1.00 |
| Diamond-plate aluminum running boards with grip strut | |
| Hidden front grille door unlock switch | 1.00 |
| Hidden front grille door unlock switch | |

Drivers Compartment

| <i>Name/Description</i> | <i>Quantity</i> |
|--|-----------------|
| Control center with pictogram labelled switches | 1.00 |
| Control center with switches and LED backlit pictograms on console | |
| Manual adjustment seat | 1.00 |
| OEM manually adjustable chassis seats. | |
| Talk-through with sliding window | 1.00 |
| Cab to module talk-through opening with sliding window | |
| Chassis voltmeter and conversion voltmeter | 1.00 |
| OEM chassis voltmeter.Digital conversion voltmeter on driver's console. | |
| Patient status indicator lights | 1.00 |
| Patient status indicator lights (Red/Yellow/Green) on driver's console | |
| Ram mount console | 1.00 |
| Ram mount console | |
| Door indicator light | 1.00 |
| "Door ajar" and "Compartment" indicator light on driver's console | |
| Two USB charging outlets | 1.00 |
| Two USB charging outlets on driver's console | |
| No floor mount console | 1.00 |
| No floor mount console | |
| Passenger reading light | 1.00 |
| Ceiling mount red/white LED reading light centered over passenger seat | |
| Driver's reading light | 1.00 |
| One (1) additional ceiling mount red/white LED reading light centered over driver seat | |

Conversion

| <i>Name/Description</i> | <i>Quantity</i> |
|---|-----------------|
| C1 Compartment, ALS Access and Battery Compartment | 1.00 |
| C1 Compartment - ALS inside/outside access with a sealed battery storage area | |
| Battery slide-out tray | 1.00 |
| Battery slide-out tray in C1 compartment | |
| C2 Side Entrance Door | 1.00 |
| C2 - Side entrance door with tinted flush mount window | |
| Dual step entry with step well light | 1.00 |
| Two-step interior access with LED step well light | |

| | |
|---|-----------------|
| C3 Compartment, Equipment Storage | 1.00 |
| Open storage in C3 Compartment | |
| C3 - Backboard storage | 1.00 |
| Dual backboard storage with straps, two adjustable shelves for equipment bags, and stair chair storage in C3 Compartment. | |
| S1 Compartment - Main Oxygen Storage | 1.00 |
| Main oxygen storage in S1 Compartment | |
| S2 Compartment - ECC | 1.00 |
| Electrical Control Center (ECC) with lower equipment storage in S2 Compartment | |
| ECC cover | 1.00 |
| Aluminum panel in ECC compartment to cover and protect electrical from water and debris | |
| S3 Compartment, Outside access closed off | 1.00 |
| Equipment storage with outside access closed off in S3 compartment | |
| 50/50 Rear doors | 1.00 |
| 50/50 Split rear entry doors with flush mounted tinted windows | |
| Black rubber fenderettes | 1.00 |
| Flexible black rubber fenderettes over rear wheels | |
| Rear kick plate with no text | 1.00 |
| Rear kick plate with no text | |
| Aluminum rub-rails on each side | 1.00 |
| Aluminum rub-rails on each side of conversion | |
| Undercoating protection | 1.00 |
| Undercoating protection | |
| Rear mudguard | 1.00 |
| Rear mudguard | |
| Rear bumper underbody | 1.00 |
| Rear bumper underbody | |
| Module front corner stone guard | 1.00 |
| Module front corner stone guard aluminum checker-plate protection | |
| Flush license plate with LED light | 1.00 |
| Flush license plate with LED light | |
| Exterior Lighting | |
| <i>Name/Description</i> | <i>Quantity</i> |
| Clearance lights | 1.00 |
| Clearance lights - Seven amber and seven red LED marker lights | |
| Two 3/4 inch red LED mid-body side lights at rear | 1.00 |
| Two 3/4 inch red LED mid-body side lights at rear to be marker top with turn signal below | |
| Two red LED brake/tail lights | 1.00 |
| Two red LED brake/tail lights | |
| Two amber LED turn lights | 1.00 |
| Two amber LED turn lights | |
| Two white LED reverse lights | 1.00 |
| Two white LED reverse lights | |
| Emergency Systems | |
| <i>Name/Description</i> | <i>Quantity</i> |
| Standard Series Emergency Lights | 1.00 |
| Standard Series Emergency Lights | |
| Colored lens | 1.00 |
| Emergency lights to have colored lenses | |

| | |
|---|-------|
| Chrome bezels | 26.00 |
| Standard Series chrome bezels | |
| Seven Whelen 900-Series emergency lights | 1.00 |
| Seven Whelen 900-Series emergency lights (Red / Red / Red / White \ Red \ Red \ Red) on front of conversion | |
| Two Whelen 700-Series red lights, one each side | 1.00 |
| Two Whelen 700-Series red intersection lights, one each side of chassis | |
| Two Whelen LIN6 Series red lights | 1.00 |
| Two Whelen LIN6 Series red lights | |
| Four Whelen 900-Series red lights (two each side) | 1.00 |
| Four Whelen 900-Series red lights (two on each side of conversion) | |
| Mid Body 700 Series above rear wheel | 1.00 |
| Two Whelen 700-Series red lights above rear wheel, one each side | |
| Four Whelen 900-series halogen scene lights | 1.00 |
| Four Whelen 900-series halogen scene lights (two on each side of conversion) | |
| Two 9x7 and one 7x3 Rear Ligh (B/A\R) | 1.00 |
| Two 9x7 and one 7x3 light (B/A\R) on rear of conversion | |
| Two Whelen 600-Series Halogen load lights | 1.00 |
| Two Whelen 600-Series Halogen load lights on rear of conversion | |
| Two 9x7 red lights at window height on rear | 1.00 |
| Two 9x7 red lights at window height on rear of conversion | |
| Siren amplifiers (100 watt) | 1.00 |
| 100 Watt Siren amplifier with 4 tones and public address (P/A) microphone | |
| Two siren speakers in front bumper | 1.00 |
| Two siren speakers in front bumper Type 1 | |

Interior Curbside Configuration

| <i>Name/Description</i> | <i>Quantity</i> |
|---|-----------------|
| Two (2) position squad bench, 6-point harness | 1.00 |
| Two position squad bench with 6-point harness system. Provides ability for second patient transport using backboard. Includes recessed waste and sharps container at head of squad bench. | |
| Squad safety net | 1.00 |
| Safety restraint net installed forward of curbside seating | |
| Curbside overhead aluminum cabinet | 1.00 |
| Overhead aluminum cabinet above curbside seating | |
| ALS Compartment | 1.00 |
| Front ALS compartment with two adjustable shelves | |
| Lockable drug cabinet | 1.00 |
| Lockable drug cabinet above ALS compartment | |

Interior Streetside Configuration

| <i>Name/Description</i> | <i>Quantity</i> |
|---|-----------------|
| CPR seat with 6-point harness system | 1.00 |
| CPR seat with 6-point harness system | |
| Fixed frames | 1.00 |
| Fixed frames with sliding polycarbonate doors | |
| Aluminum countertop | 1.00 |
| Aluminum countertop - Powder coated | |

Attendant Seat

| <i>Name/Description</i> | <i>Quantity</i> |
|-------------------------|-----------------|
|-------------------------|-----------------|

| | |
|---|-----------------|
| Child safety device | 1.00 |
| Rear-facing EVS seamless vinyl seat with child safety device and 3-point seatbelt | |
| Box Base with front/rear slider | 1.00 |
| Box Base with front/rear slider | |
| Cot Configuration | |
| <i>Name/Description</i> | <i>Quantity</i> |
| Stryker universal floor plate only | 1.00 |
| Stryker universal floor plate only | |
| Center mount cot configuration | 1.00 |
| Center mount cot configuration | |
| Oxygen | |
| <i>Name/Description</i> | <i>Quantity</i> |
| Quick disconnect style outlet | 1.00 |
| Quick disconnect style outlet | |
| Universal vertical holder | 1.00 |
| Universal vertical holder for oxygen cylinder | |
| One oxygen outlet in Action Area | 1.00 |
| One oxygen outlet in Action Area | |
| One additional oxygen outlet in Action Area | 1.00 |
| One additional oxygen outlet in Action Area | |
| One oxygen outlet on curbside wall | 1.00 |
| One oxygen outlet on curbside wall | |
| Electrical | |
| <i>Name/Description</i> | <i>Quantity</i> |
| Multiplex system | 1.00 |
| Multiplex electrical system using toggle switches with LED backlit pictogram. | |
| Curbside switch panel | 1.00 |
| Curbside switch panel | |
| Rear speaker volume control | 1.00 |
| Rear speaker volume control at Action Area | |
| Temperature control with automatic setting | 1.00 |
| Temperature control with automatic setting at Action Area. | |
| Patient status indicator lights | 1.00 |
| Patient status indicator lights (Red/Yellow/Green) at Action Area. | |
| On/off LED reading light | 1.00 |
| On/off LED reading light above Action Area. | |
| Four antenna ports with pre-wiring | 1.00 |
| Four antenna ports with pre-wiring for antenna RG 58 A/U | |
| Two OEM batteries | 1.00 |
| Two OEM batteries | |
| Additional 3rd battery | 1.00 |
| Additional 3rd battery | |
| Back up alarm | 1.00 |
| Back-up alarm (97db) | |
| High intensity LED compartment rope lights | 1.00 |
| High intensity LED compartment rope lights | |
| Six LED dome lights | 1.00 |
| Six LED dome lights with multiple intensity settings | |
| Xantrex Freedom XC pure sine-wave inverter/charger | 1.00 |
| Xantrex Freedom XC pure sine-wave inverter/charger | |

| | |
|---|------|
| Auto Eject - Yellow 20 amps | 1.00 |
| Auto-eject shoreline outlet - 120V 20 amp assembly with a yellow waterproof cover | |
| Shoreline light | 1.00 |
| Indicator light above the shoreline plug to show power connection | |
| 1 120V GFCI outlet in Action Area | 1.00 |
| One Hospital-grade 120 VAC GFCI dual outlet with indicator light in Action Area | |
| 1 120V outlet in lower ALS area | 1.00 |
| One Hospital-grade 120 VAC dual outlet with indicator light in lower ALS area | |
| 1 120V outlet in upper ALS area | 1.00 |
| One Hospital-grade 120 VAC dual outlet with indicator light in upper ALS area | |
| One 12 VDC outlet in lower ALS area | 1.00 |
| One 12 VDC outlet in lower ALS area | |
| One 12 VDC outlet in Action area | 1.00 |
| One 12 VDC outlet in Action area | |
| Camera monitor in cab | 1.00 |
| Camera monitor in cab | |
| Back-up camera | 1.00 |
| Back-up camera | |
| Rico RS4X disposable suction system | 1.00 |
| Rico RS4X disposable suction system in Action Area | |

HVAC

| <i>Name/Description</i> | <i>Quantity</i> |
|---|-----------------|
| Combo heat and AC | 1.00 |
| Combo heat and air conditioning with exhaust fan for contaminated air | |

Accessories

| <i>Name/Description</i> | <i>Quantity</i> |
|--|-----------------|
| Three glove box holder above side entry door | 1.00 |
| Three glove box holder above side entry door | |
| Recessed digital clock above rear entry doors | 1.00 |
| Digital clock recessed above rear entry doors | |
| No fire extinguisher in chassis | 1.00 |
| No fire extinguisher in chassis cab | |
| No fire extinguisher in S3 compartment | 1.00 |
| No fire extinguisher in S3 compartment | |
| L-shaped yellow grab bar on side entry door | 1.00 |
| L-shaped yellow grab bar on side entry door | |
| L-shaped yellow grab bars on rear entry doors | 1.00 |
| L-shaped yellow grab bars on rear entry doors | |
| One 61in ceiling mounted grab rail | 1.00 |
| One 61in ceiling mounted yellow grab rail | |
| Four clip style IV hangers with strap | 1.00 |
| Four clip style IV hangers with strap (2 curbside wall, 2 streetside wall) | |
| Spare plastic trash liners | 1.00 |
| Twelve spare plastic trash liners | |

Finish and Trim

| <i>Name/Description</i> | <i>Quantity</i> |
|---|-----------------|
| Interior powdercoated white | 1.00 |
| Cabinets, wall panels and ceiling are white powder-coated aluminum | |
| Black upholstery | 1.00 |
| Black vinyl upholstery with yellow head bolster pads on entry doors | |

| | |
|--|-----------------|
| Floor : Slip resistant, rolled-up 5 in. (127mm) | 1.00 |
| Floor : Slip resistant, rolled-up 5 in. (127mm) | |
| Lonplate II Midnight #443TXM | 1.00 |
| Lonplate II Midnight #443TXM flooring | |
| Clear anti-slip spray | 1.00 |
| Clear anti-slip spray applied to side entry steps | |
| Paint and Graphics | |
| <i>Name/Description</i> | <i>Quantity</i> |
| Powdercoat module white | 1.00 |
| Powdercoat entire module white to match the chassis | |