

## Specification Summary

**Purchaser:** North Eastern Rescue Vehicles  
**Contact:** Bob Reilly  
**Address:** 10 Dwight Park Drive  
 Syracuse, NY

North Eastern Rescue Vehicles, Inc.  
 Bob Reilly  
 10 Dwight Park Drive  
 Syracuse, NY 13209  
 UNITED STATES

**Name**

**CCL150**



**Specifications**

- Aluminum Extruded Body Construction
- CrestCoat Powder Coating Technology
- Aluminum Cabinets
- Multiplex Electrical System
- Flush Mount Windows

### Sales Options by Category

**Base**

Name/Description	Quantity
<b>TYPE III - CCL150</b>	
TYPE III - CCL150	1.00
<b>68in Interior Headroom</b>	
68 inch Interior Headroom	1.00
<b>KKK-A-1822F</b>	
KKK-A-1822F - USA Government Federal Specification for a Star-of-Life Ambulance	1.00

**Chassis**

Name/Description	Quantity
<b>GM 3500 Express Cutaway Chassis</b>	1.00

Chevrolet G3500 Express Gas Cutaway 4X2 1396,0L Vortec V8 Gasoline  
 EngineWheelbase 139 (4039 mm)GVWR (Gross vehicle weight rating) 12,300 Lbs /  
 5,579 Kg

<b>Anti-theft</b>	1.00
Anti-theft security system	
<b>High Idle</b>	1.00
High Idle system	
<b>G-Series Velvac remote and heated chassis mirrors</b>	1.00
Velvac 2020XG remote and heated chassis mirrors	
<b>Wheel alignment</b>	1.00
Wheel alignment completed at the factory	
<b>Running Boards</b>	1.00
Diamond-plate aluminum running boards with grip strut	
<b>Hidden front grille door unlock switch</b>	1.00
Hidden front grille door unlock switch	

**Drivers Compartment**

Name/Description	Quantity
<b>Control center with pictogram labelled switches</b>	1.00
Control center with switches and LED backlit pictograms on console	
<b>Recessed cab into module</b>	1.00
Recessed cab into module, allowing cab seats to recline	
<b>Manual adjustment seat</b>	1.00
OEM manually adjustable chassis seats.	
<b>Talk-through with sliding window</b>	1.00
Cab to module talk-through opening with sliding window	
<b>Two coat hooks</b>	1.00
Two coat hooks on chassis side of bulkhead	
<b>Narrow center console</b>	1.00
Narrow center console	
<b>Chassis voltmeter and conversion voltmeter</b>	1.00
OEM chassis voltmeter.Digital conversion voltmeter on driver's console.	
<b>Patient status indicator lights</b>	1.00
Patient status indicator lights (Red/Yellow/Green) on driver's console	
<b>Door indicator light</b>	1.00
"Door ajar" and "Compartment" indicator light on driver's console	
<b>Two USB charging outlets</b>	1.00
Two USB charging outlets on driver's console	
<b>No floor mount console</b>	1.00
No floor mount console	
<b>Passenger reading light</b>	1.00
Ceiling mount red/white LED reading light centered over passenger seat	
<b>Driver's reading light</b>	1.00
One (1) additional ceiling mount red/white LED reading light centered over driver seat	

**Conversion**

Name/Description	Quantity
<b>C1 Compartment, ALS Access and Battery Compartment</b>	1.00
C1 Compartment - ALS inside/outside access with a sealed battery storage area	
<b>C2 Side Entrance Door</b>	1.00
C2 - Side entrance door with tinted flush mount window	
<b>Dual step entry with step well light</b>	1.00
Two-step interior access with LED step well light	

<b>C3 Compartment, Equipment Storage</b>	1.00
Open storage in C3 Compartment	
<b>C3 - Backboard storage</b>	1.00
Dual backboard storage with straps, two adjustable shelves for equipment bags, and stair chair storage in C3 Compartment.	
<b>S1 Compartment - Main Oxygen Storage</b>	1.00
Main oxygen storage in S1 Compartment	
<b>S2 Compartment - ECC</b>	1.00
Electrical Control Center (ECC) with lower equipment storage in S2 Compartment	
<b>ECC cover</b>	1.00
Aluminum panel in ECC compartment to cover and protect electrical from water and debris	
<b>S3 Compartment, Inside/Outside Equipment Storage</b>	1.00
Equipment storage with upper inside/outside access in S3 Compartment	
<b>Two adjustable shelves</b>	1.00
Two adjustable shelves in S3 Compartment	
<b>50/50 Rear doors</b>	1.00
50/50 Split rear entry doors with flush mounted tinted windows	
<b>Black rubber fenderettes</b>	1.00
Flexible black rubber fenderettes over rear wheels	
<b>Rear kick plate with no text</b>	1.00
Rear kick plate with no text	
<b>Aluminum rub-rails on each side</b>	1.00
Aluminum rub-rails on each side of conversion	
<b>Undercoating protection</b>	1.00
Undercoating protection	
<b>Rear mudguard</b>	1.00
Rear mudguard	
<b>Rear bumper underbody</b>	1.00
Rear bumper underbody	
<b>Module front corner stone guard</b>	1.00
Module front corner stone guard aluminum checker-plate protection	
<b>Flush license plate with LED light</b>	1.00
Flush license plate with LED light	

**Exterior Lighting**

<i>Item Number</i>	<i>Name/Description</i>	<i>Quantity</i>
	<b>Clearance lights</b>	1.00
	Clearance lights - Seven amber and seven red LED marker lights	
	<b>Two 3/4 inch red LED mid-body side lights at rear</b>	1.00
	Two 3/4 inch red LED mid-body side lights at rear to be marker top with turn signal below	
	<b>Two red LED brake/tail lights</b>	1.00
	Two red LED brake/tail lights	
	<b>Two amber LED turn lights</b>	1.00
	Two amber LED turn lights	
	<b>Two white LED reverse lights</b>	1.00
	Two white LED reverse lights	
	<b>High center mounted brake light feature</b>	1.00
	High center mounted brake light feature	

**Emergency Systems**

<i>Name/Description</i>	<i>Quantity</i>
-------------------------	-----------------

<b>Colored lens</b>	1.00
Emergency lights to have colored lenses	
<b>Chrome bezels</b>	24.00
Standard Series chrome bezels	
<b>Two Whelen 900-Series and three 700-Series lights</b>	1.00
Two Whelen 900-Series and three 700-Series lights (Red / Red / White \ Red \ Red) on front of conversion	
<b>Two Whelen 700-Series red lights, one each side</b>	1.00
Two Whelen 700-Series red intersection lights, one each side of chassis	
<b>Two Whelen 500-Series red lights</b>	1.00
Two Whelen 500-Series red lights in grille	
<b>Four Whelen 900-Series red lights (two each side)</b>	1.00
Four Whelen 900-Series red lights (two on each side of conversion)	
<b>Mid Body 700 Series above rear wheel</b>	1.00
Two Whelen 700-Series red lights above rear wheel, one each side	
<b>Four Whelen 900-series halogen scene lights</b>	1.00
Four Whelen 900-series halogen scene lights (two on each side of conversion)	
<b>Two Whelen 900-Series and one 700-Series lights</b>	1.00
Two Whelen 900-Series and one 700-Series lights (Red / Amber \ Red) on rear of conversion	
<b>Two Whelen 600-Series Halogen load lights</b>	1.00
Two Whelen 600-Series Halogen load lights on rear of conversion	
<b>Two 9x7 red lights at window height on rear</b>	1.00
Two 9x7 red lights at window height on rear of conversion	
<b>Siren amplifiers (100 watt)</b>	1.00
100 Watt Siren amplifier with 4 tones and public address (P/A) microphone	
<b>Two siren speakers in front grille</b>	1.00
Two siren speakers in front grille Type 3	

**Interior Curbside Configuration**

<i>Name/Description</i>	<i>Quantity</i>
<b>Two (2) position squad bench, 6-point harness</b>	1.00
Two position squad bench with 6-point harness system. Provides ability for second patient transport using backboard. Includes recessed waste and sharps container at head of squad bench.	
<b>Squad safety net</b>	1.00
Safety restraint net installed forward of curbside seating	
<b>ALS Compartment</b>	1.00
Front ALS compartment with two adjustable shelves	
<b>Drug cabinet</b>	1.00
Drug cabinet above ALS compartment	

**Interior Streetside Configuration**

<i>Name/Description</i>	<i>Quantity</i>
<b>CPR seat with 6-point harness system</b>	1.00
CPR seat with 6-point harness system	
<b>Fixed frames</b>	1.00
Fixed frames with sliding polycarbonate doors	
<b>Aluminum countertop</b>	1.00
Aluminum countertop - Powder coated	

**Attendant Seat**

<i>Item Number</i>	<i>Name/Description</i>	<i>Quantity</i>
--------------------	-------------------------	-----------------

<b>Child safety device</b>	1.00
Rear-facing EVS seamless vinyl seat with child safety device and 3-point seatbelt	
<b>Box Base with front/rear slider</b>	1.00
Box Base with front/rear slider	
<b>Cot Configuration</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Stryker universal floor plate only</b>	1.00
Stryker universal floor plate only	
<b>Pre-wire Performance-LOAD</b>	1.00
Pre-wire Performance-LOAD	
<b>Center mount cot configuration</b>	1.00
Center mount cot configuration	
<b>Oxygen</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Quick disconnect style outlet</b>	1.00
Quick disconnect style outlet	
<b>Universal vertical holder</b>	1.00
Universal vertical holder for oxygen cylinder	
<b>One oxygen outlet in Action Area</b>	1.00
One oxygen outlet in Action Area	
<b>One ceiling mounted oxygen outlet</b>	1.00
One ceiling mounted oxygen outlet	
<b>One oxygen outlet on curbside wall</b>	1.00
One oxygen outlet on curbside wall	
<b>Electrical</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Multiplex system</b>	1.00
Multiplex electrical system using toggle switches with LED backlit pictogram.	
<b>Rear speaker volume control</b>	1.00
Rear speaker volume control at Action Area	
<b>Temperature control with automatic setting</b>	1.00
Temperature control with automatic setting at Action Area.	
<b>Patient status indicator lights</b>	1.00
Patient status indicator lights (Red/Yellow/Green) at Action Area.	
<b>On/off LED reading light</b>	1.00
On/off LED reading light above Action Area.	
<b>Four antenna ports with pre-wiring</b>	1.00
Four antenna ports with pre-wiring for antenna RG 58 A/U	
<b>Two OEM batteries</b>	1.00
Two OEM batteries	
<b>Back up alarm</b>	1.00
Back-up alarm (97db)	
<b>Round LED compartment lighting</b>	1.00
Round LED compartment lighting	
<b>Six LED dome lights</b>	1.00
Six LED dome lights with multiple intensity settings	
<b>Xantrex Freedom XC pure sine-wave inverter/charger</b>	1.00
Xantrex Freedom XC pure sine-wave inverter/charger	
<b>Auto Eject - Yellow 20 amps</b>	1.00
Auto-eject shoreline outlet - 120V 20 amp assembly with a yellow waterproof cover	

<b>Shoreline light</b>	1.00
Indicator light above the shoreline plug to show power connection	
<b>1 120V GFCI outlet in Action Area</b>	1.00
One Hospital-grade 120 VAC GFCI dual outlet with indicator light in Action Area	
<b>1 120V outlet in upper ALS area</b>	1.00
One Hospital-grade 120 VAC dual outlet with indicator light in upper ALS area	
<b>One 12 VDC outlet in lower ALS area</b>	1.00
One 12 VDC outlet in lower ALS area	
<b>One 12 VDC outlet in Action area</b>	1.00
One 12 VDC outlet in Action area	
<b>Camera monitor in cab</b>	1.00
Camera monitor in cab	
<b>Back-up camera</b>	1.00
Back-up camera	
<b>Rico RS4X disposable suction system</b>	1.00
Rico RS4X disposable suction system in Action Area	

### HVAC

<i>Name/Description</i>	<i>Quantity</i>
<b>Combo heat and AC</b>	1.00
Combo heat and air conditioning with exhaust fan for contaminated air	

### Accessories

<i>Name/Description</i>	<i>Quantity</i>
<b>Three glove box holder above side entry door</b>	1.00
Three glove box holder above side entry door	
<b>Analog clock above rear entry doors</b>	1.00
Analog clock mounted above rear entry doors	
<b>No fire extinguisher in chassis</b>	1.00
No fire extinguisher in chassis cab	
<b>5lb fire extinguisher with bracket in S3</b>	1.00
5lb fire extinguisher with heavy duty bracket installed in S3 compartment	
<b>L-shaped yellow grab bar on side entry door</b>	1.00
L-shaped yellow grab bar on side entry door	
<b>L-shaped yellow grab bars on rear entry doors</b>	1.00
L-shaped yellow grab bars on rear entry doors	
<b>One 61in ceiling mounted grab rail</b>	1.00
One 61in ceiling mounted yellow grab rail	
<b>Technimount monitor mounting base</b>	1.00
Technimount monitor mounting base.	
<b>Four clip style IV hangers with strap</b>	1.00
Four clip style IV hangers with strap (2 curbside wall, 2 streetside wall)	
<b>Spare plastic trash liners</b>	1.00
Twelve spare plastic trash liners	

### Finish and Trim

<i>Name/Description</i>	<i>Quantity</i>
<b>Interior powdercoated white</b>	1.00
Cabinets, wall panels and ceiling are white powder-coated aluminum	
<b>Black upholstery</b>	1.00
Black vinyl upholstery with yellow head bolster pads on entry doors	
<b>Floor : Slip resistant, rolled-up 5 in. (127mm)</b>	1.00
Floor : Slip resistant, rolled-up 5 in. (127mm)	

<b>Lonplate II Midnight #443TXM</b>	1.00
Lonplate II Midnight #443TXM flooring	
<b>Clear anti-slip spray</b>	1.00
Clear anti-slip spray applied to side entry steps	
<b>Stainless steel wall protection from cot</b>	1.00
Stainless steel wall protection on lower streetside cabinet and on lower squad bench	
<b>Paint and Graphics</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Powdercoat module white</b>	1.00
Powdercoat entire module white to match the chassis	