



## QUOTATION

North Eastern Rescue Vehicles, Inc  
Bob Reilly  
10 Dwight Park Drive  
Syracuse, NY 13209

Job/Order No: 628335

WO#: 628335

Page 1

DESCRIPTION	QTY		
<b>WARRANTY</b>			
WC, Warranty, Conversion, 12 Month	1		
WC, Warranty, Paint, 60 month Prorated	1		
WC, Warranty, Structural, 20 Years, Std., Mods	1		
WC, Warranty, Limited Electrical	1		
WC, Warranty, Cabinet Construction	1		
<b>== WC- Type 1 CitiMedic Gen2 148"</b>			
This unit built in accordance with KKK-A-1822-F in effect on the date of order with exceptions as noted herein.	1		
MD, This unit built in accordance with KKK-A-1822F CN 10 Cabinet Requirements	1		
This unit as specified meets all requirements of KKK-A1822-F Change notice 10.			
All cabinets shall be labeled as to their capacity Rating.			
<b>01- CHASSIS REQUIREMENTS</b>			
<b>FORD CHASSIS</b>			
CM, 2024 Ford F350, 4x4, 6.7L ,169" WB 2022-8	1		
Auto throttle OEM Ford			
Dual Alternators OEM Ford			
Mirrors, OEM, Heated/Remote			
Cab seats OEM 40/20/40 split bench (Center removed)			
Sync 3			
Enhanced voice recognition communication and entertainment system			
8" LCD Capacitive Touch screen in center stack w/swipe Capability			
Pinch to Zoom capability			
AppLink			
911 assist			
Apple carPlay and Android Auto			
Smart-charging USB-C Ports (2)			
Domestic Chassis	1		

DESCRIPTION	QTY		
<b>ALTERNATORS</b>			
Alternator - Standard OEM	1		
<b>SUSPENSION</b>			
Rear Suspension, OEM Springs	1		
<b>HIGH IDLE</b>			
High Idle Controls, OEM	1		
<b>FRONT END ALIGNMENT</b>			
Front End Alignment, None- QC Check	1		
CM,Wheeled Coach Stainless Grille Logo, with Red Reflective backing	1		
Red reflective behind cut out.			
<b>OUTSIDE REAR VIEW MIRRORS</b>			
Mirrors, OEM-STD	1		
<b>WHEEL COVERS</b>			
CM, Wheel Covers, Phoenix, Ford Type 1, Installed with Air Max Valve Extenders	1		
<b>BASE CONVERSION</b>			
CM, Conversion, Type 1, 148 Module, F350 4x4 - 23-1	1		
<b>MODULE BODIES:</b>			
CM, Interior Headroom, 68 Inches	1		
CM, Module, Type 1, 148" Body Length, 90" Wide, Duraseam Doors,	1		
148" L x 90" W			
CM, Aisle Space, 49", CityMedic Plus (48-49" actual)	1		
<b>EXTERIOR MODULE CONSTRUCTION</b>			
CM, Stone Guard, Front, Diamond Plate, Type 1 Height	1		
<b>DROP SKIRTS</b>			
CM, Drop Skirt both sides, 3" forward of rear wheels	1		
<b>FUEL FILLS &amp; SPLASH PLATE</b>			
CM, Housing Fuel Fill, Cast, Type 1	1		
CM, DEF Fill, Housing, For Ford F series	1		
<b>REAR KICKPLATE</b>			
CM, Rear Kick plate,Under-Ride Bumper, w/ Tag recess, No lights, CM+	1		
<b>SUB-FLOOR SYSTEM</b>			
CM, Flooring, 3/4" Marine Grade Plywood, Type 1	1		
<b>MODULE ENTRANCE</b>			
<b>MODULE DOORS, HANDLES &amp; HOLD OPENS</b>			
CM, Duraseam Hinged Doors with Hidden Jambs - Magnetic door switches	1		
CM, Hold Open Rear Entry Doors, (2) 5.5" Cast Grabber - Installed so doors will open as wide as possible - Mount at Bottom of doors.	1		
CM, Hold Open, Gas Strut, Curb Side Entry Door, 35#	1		
CM, Patient Entry Door Handles, Trimark Black/Chrome Pull Handle w/"Push Button"	1		
With Round Push button Emergency release top and bottom of interior door panels.			

DESCRIPTION	QTY		
CM, Rear Entry Door Trailing Latch, Side release Paddle	1		
CM, Electrical Feed to Required Doors, Spring Protector (Per Door)	7		
<b>POWER DOOR LOCKS</b>			
CM, Power Door Lock, Trimark, Each Entry Door <i>Module entry doors.</i>	2		
CM, Power Door Lock, Trimark, Each Compartment Door <i>All module compartments</i>	5		
CM, Power Door Locks, All Module doors (except Batt) Wiring to Module Compartment and Access Doors (except Battery) for electric locks, wiring to CS wall for Switch.	1		
Includes the Tie in to the Cab door lock switches.			
CM, Intermotive CAN module for 2017+ Ford F-series	1		
CM, Relay Control Circuit, Power Door Locks	1		
CM, Circuit, OEM Door Lock to activate Mod Doors (Not Dodge)	1		
<b>ENTRY DOOR INNER PANELS</b>			
CM, Entry Panels, Durasafe, Stainless Steel, w/ Center Chevrons <i>- Durasafe Design</i> <i>- Aluminum Center Panels covered: reflective tape</i> <i>Upper and Lower door panels Stainless Steel</i> <i>Center lock box aluminum with white/DOT BLUE reflective tape</i>	1		
<b>SIDE DOOR STEP</b>			
CM, Side Entry Step Well, Type I, Aluminum Diamond Plate	1		
CM, Double Step Well	1		
CM, Light, Side Entry Step well, LED, 2", Whelen #TOCACCCR	1		
<b>WINDOWS</b>			
CM, Window, Upper, CS/Slider ,Rr/Fixed, Privacy Tint, PAN Curbside window with lower slider section Rear windows fixed Privacy Tint	1		
<b>CAB TO MODULE</b>			
CM, Bellows, Crawl-thru, Cab Height, Ford Type 1, <b>REAR BUMPER AND REAR STEP CONSTRUCTION</b>	1		
CM, Rear Bumper, Ford Type 1, w/LED Lights <i>with Gator Grip on flip up step.</i> <i>Lights in side of bumper pod Steady burn with lights on</i>	1		
CM, BLACK Polyurethane Coating, Rear Bumper Supports	1		
<b>INSULATION</b>			
CM, Insulation, Fiberglass, Un faced	1		
<b>RUB RAIL AND FENDER RINGS</b>			
CM, Rub Rails, Skirt Line, Extruded "C" channel (E-one Style), 148"	1		
CM, Tape, Reflective, White, For Extruded Skirt rails	1		
CM, Fender Flare, Black Rubber	1		
<b>SPLASH GUARDS AND RUNNING BOARDS</b>			
CM, Mud Flaps, Rear, w/ Wheeled Coach Logo	1		
CM, Running Boards, Ford Type 1, w/Gator Grip, <b>CAB TO PATIENT AREA ACCESS</b>	1		

DESCRIPTION	QTY		
CM, Bulkhead, Cabinet, Crawl-Thru, Type 1	1		
CM, Bulkhead, Door, Sliding w/Sliding Window with sliding Lexan window	1		
<b>LICENSE PLATE HOLDER</b>			
CM, License Plate Holder, Cast LP0002, for Under ride Bumper in rear kick plate, centered License holder comes with (2) LED lights.	1		
<b>EXTERIOR COMPARTMENT CONSTRUCTION</b>			
CM, Compartments, Floor Drop Down Compartment #6 (more than 2.5" for spare tire) Compartment #2 -2.5" drop-down Compartment #4, 4" drop-down	3		
CM, Compartments, Sweep out Compartments #1 & #8 are standard sweep out	2		
CM, Door Sill Protector, Stainless, All Comps	1		
CM, Compartments, Diamond Plate Finish Per Comp Machine stamped louvers located above the floor line for venting.	4		
Comp #2,4,6			
Comp #1 to have Baffle vent			
CM, Exterior Battery Compartment, Diamond Plate Finish	1		
<b>EXTERIOR COMPARTMENT DOORS</b>			
CM, Compartment Comp Handle, Trimark, Oval Pull Handle, Black/Chrome	5		
<b>COMPARTMENT DOOR HOLD OPEN</b>			
CM, Hold Open, Gas Strut, Ext Comp, 60lb Compartment "#4", standard	1		
CM, Hold Open, Gas Strut, Ext Comp, 30lb. Compartments "#6", "#1", & "#2"	3		
CM, Hold Open, Gas Strut, RF Comp, 30lb	1		
<b>COMPARTMENT LIGHTING</b>			
CM, Oxygen Light, 3" Surface mount Whelen LED, Clear Mounted in Oxygen Compartment	1		
CM, Compartment Light, 4" Optronic, #BUL43-CBK, LED, Each Compartment	6		
1 - Access Panel Wall 1			
2 - Wall #1			
4 - Ceiling			
6 - Wall #3			
8- Wall #3 in access panel U8			
8- Wall #3 in access panel L8			
<b>COMPARTMENT #1 - STREETSIDE FWD</b>			
CM, Compartment #1, 3/4 High, CitiMedic.	1		
<b>COMPARTMENT #2 - STREETSIDE FWD WHEELWELL</b>			

DESCRIPTION	QTY		
CM, Compartment #2, Citimedic, Type 1 <b>Mount the inverter on the ceiling of compartment.</b>	1		
CM, Compartment #2, Shelf, ADP, Fixed for Electrical storage Screw in shelf that extends from wall 1 to the recessed suction and wall 2 to flush with the face of the suction dogleg	1		
Add Dogleg in Comp #2 for Recessed Suction in Face of A/A	1		
<b>COMPARTMENT #4 - STREETSIDE AFT</b>			
CM, Compartment #4, Full Height, Dual Depth, Citimedic - Full height backboard storage on the #4 compartment door. - The upper section is 8" D due to dogleg for interior cabinetry. Bottom section is 15" deep.	1		
Floor drop of 4" for the entire compartment			
CM, Compartment #4, Strap, Seat Belt Style, Each (1) on comp #4 door for Backboards	2		
(1) from wall #1 to Wall #3 about 6" from wall 2 for the Stair chair.			
CM, Compartment #4, Bracket, Backboard Mount on Door Diamond plate "C-style boxes mounted to the door of Comp #4	1		
one at top and bottom to allow backboards or scoop stretcher to be slid in from the outboard side.			
<b>COMPARTMENT #6 - CURBSIDE AFT</b>			
CM, Compartment #6, Spare Tire, <b>With special Drop pan for spare tire.</b> <b>Do NOT install spare tire bracket.</b>	1		
<b>COMPARTMENT #8 - CURBSIDE UPPER FORWARD</b>			
CM, Compartment #8/8.5, Single Door, Type 1 Single door with inside /outside access, upper area.	1		
Outside access only to lower aluminum area.			
Battery storage, under hood.			
CM, Compartment #8, Shelf, Adjustable, First Shelf RF Comp "8"/cabinet "U8" area - centered top to bottom.	1		
CM, Compartment #8, Shelf, Additional, Adjustable, Each RF Comp "8"/cabinet "L8" area centered top to bottom.	1		
<b>INTERIOR TRIM AND FEATURES</b>			
CM, Interior Cabinets, Duralite Construction, Wood	1		
CM, Cabinet Shelf, Interior, Wood, Adjustable, First shelf <b>Cabinet U4, will have 4 adjustable shelves</b>	1		
CM, Cabinet Shelf, Interior, Wood, Additional, Adjustable Cabinet U4	3		
CM, Cabinet Shelf Track, #HA24663, Upgrade, CN 10 <b>("C" channel/exterior shelf style track)</b>	1		

DESCRIPTION	QTY		
<b>Cabinet U4</b>			
<b>HEADLINER</b>			
CM, Headliner, Flat, PVC, Hinged trough cover, Std	1		
<b>FLOORING</b>			
CM, Flooring, Lonplate II, Gunpowder Gray #424TX	1		
CM, Flooring, Roll up, 3-4" Approx....., No Toe Kick	1		
The roll up is not recessed it is installed on the cabinet wall and Squad bench.			
CM, Floor, Thresholds, .063 Aluminum, Painted w/Black Poly-urea coating	1		
<b>GRAB RAILS</b>			
<b>Rear Entry Door Grab Handles</b>			
CM, Entry Door Grab Handles (3), "L" Shape, 1", Yellow	1		
<b>Yellow Powder Coat Finish Stainless Steel Grab Handles</b>			
<b>Ceiling Grab Rail - Center</b>			
CM, Ceiling Grab Rail, Overhead, 84", 1" Diameter Handicap Style, Yellow	1		
Yellow Powder Coat Finish			
<b>IV FLUID HANGERS</b>			
CM, IV Hangers, Perco (1), W/Straps Each	2		
<b>Location: Standard SS and CS locations</b>			
<b>BASEWALL CABINET:</b>			
CM, Cabinet, Base wall, Type 1, CPR Seat, w/Telemetry Area	1		
<b>Cabinet L3.5</b>			
CM, Cabinet, Street side Upper, 148 Module, w/CPR Seat , 68" HR	1		
<b>Cabinet U2, U1 wood door</b>			
CM, Street side rear, with side seat, 68" HR	1		
<b>Cabinet U3.5, U4</b>			
CM, Tray, A/A, Std Aisle No Bio waste, Poured, Black	1		
CM, Door, U1 Hinged Wood	1		
<b>hinged on right.</b>			
<b>U1 cabinet will be used as a locking drug cabinet.</b>			
CM, Door, U2 Gray Poly carbonate Slider, CN 10 Compliant	1		
<b>Interior Street side #3 - CPR Seat</b>			
CM, CPR side seat, Fixed Backrest	1		
CM, CPR, Lid, Hinged Flip Up	1		
With Trimark Latch			
CM, Door, U3.5, OHO Top Hinged Gray Poly carbonate (CWTG) CN 10 Complia	1		
CM, Door, L3.5, OHO Bottom Hinged Gray Poly carbonate, (CWBD) CN 10 Comp	1		
CM, Door, U4, OHO Dual Hinged Gray Poly carbonate (CWDX) CN 10 Compliant	1		
CM, CPR Seat, "U" Barrier Bar, Padded, 1.5" SS, Gunmetal	1		
<b>Mounted at the front of the CPR side seat vertically in line with the Padded head cushion on the cabinets.</b>			

DESCRIPTION	QTY		
CM, Telemetry Tray, Poured, Black	1		
<b>SQUAD BENCH AREA</b>			
CM, Cabinet, Squad Bench, CM+, w/ Bio waste	1		
With Bio waste at the head of the squad bench cabinet.			
CM, Lid, Squad Bench, Single W/Bio-Waste Must use M1 latch for CN 10 on bio waste door Lift up lid ONLY over storage area	1		
CM, Squad Bench, Handle, Trimark, STD	1		
CM, Strut, Gas, 30 LB, Installed	1		
CPR seat lid			
CM, Strut, Gas, 60 LB, Installed	1		
Squad bench lid			
CM, CPR, Handle, Trimark, STD	1		
CM, Bio-waste Cover, Etched Red Plastic	1		
<b>SEAT BELTS/ SAFETY NETS</b>			
CM, CPR Seat, Seatbelt, Assy, (4 Point), Per4Max, Yellow, (1) Each, CN-8	1		
CPR side seat Above the lid			
CM, Squad Bench, Seatbelt, Assy, (4 Point) Per4Max, Yellow, (2) Each Above the lid On squad bench	1		
CM, Patient Restraint Belts, Squad Bench (3)	1		
CM, Safety Net, Head of Squad Bench, 2" Straps, Yellow attached to floor at head of squad bench, CS wall and overhead liner with removable latches.	1		
<b>CURBSIDE REAR</b>			
CM, Cabinet, Curbside Rear, In Rear wall, U6,C6 Gray OHO doors (1) adjustable shelf in cabinet U6 (1) adjustable shelf in cabinet C6	1		
<b>BIOHAZARD-</b>			
CM, Glove Butler-Cabinet, (3),Above C/S door Must use M1 latches for KKK Change notice 10 certification	1		
<b>CURBSIDE RIGHT STACK STORAGE #8</b>			
CM, RF ALS, Split Upper/Lower, HVAC at Top	1		
CM, Doors, RF, U8, Dual Gen III OHO, Poly carbonate Doors, Gray	1		
CM, Doors, RF, L8, Dual Gen III OHO, Poly carbonate Doors, Gray	1		
<b>ATTENDANT SEAT</b>			
CM, Attendant's Seat, EVS 1880,Comfort, Hi-Back Child Safety w/Per4Max	1		
CM, Color, Gunmetal, Per4Max Belt, Yellow	1		
CM, Door, Diamond Plate, EVS Seat Base, M1 Latch	1		
CM, Attendant's Seat Base, EVS CBS Box Style	1		
Box opening to be toward CURBSIDE access door """"TO BE MOUNTED AS FAR FORWARD AS POSSIBLE TO MAXIMIZE KNEE ROOM""""			

DESCRIPTION	QTY		
<b>INTERIOR COLORS</b>			
CM, Mica, Dove Gray (Matte)	1		
<b>UPHOLSTERY</b>			
CM, Upholstery, Seamless, Gunmetal	1		
CM, Backrest Cushion, EVS, Gunmetal, w/ WC Logo, Each	2		
CM, Backrest Cushion, EVS, Gunmetal, w/ WC Logo, Each	1		
CM, Marine Hasp, for Padlock Installed on U-1 cabinet	1		
<b>CABINET KICK PANELS</b>			
CM, Kick plate, Brushed SS, Face of S/B & Base wall, 148 CM	1		
<b>CABINET LATCHES- INTERIOR</b>			
CM, Latch, Southco, Lever, Chrome, Non Locking, CN 10-Rated 5lb Cabinet U1	1		
CM, Latch, M1, 3/4" Material, 2" round, Non Locking, Chrome-CN 10 Certified Sharps/Waste	1		
CM, Latch, Southco M1, 2" S/S, (3/8" Door) Non-Locking, CN 10-Rated 10lb (self latching) Flush Mount. Non-Locking On glovebox cabinet above C/S entry door	1		
<b>06 - ELECTRICAL GENERAL</b>			
CM, 12V Electrical system, RelayPlex system Flash Pattern- Quad Flash 75 - Per KKK	1		
<b>COMMUNICATION</b>			
CM, Coax Cable, RG58/U, Each, Terminate: CS Dome #2 to behind pass seat with 6' pigtails S/S Dome #4 to behind the drivers seat with 6' pigtails S/S Dome #5 to behind the pass seat with 6' pigtails	3		
CM, Light, in Circuit Board Area, for Electrical Troubleshooting - with integral switch; wired constant hot.	1		
<b>POWER SOURCES</b>			
CM, Power Source, 12VDC, 20A, Ignition/Shoreline Hot 20amp 12 volt DC circuit routed to two locations, (1) pre-wire coil and tagged in action area and (1) pre-wire coil and tagged behind driver's seat.	1		
CM, Power Source, 12 VDC, 15 Amp (+-), Std Model only - Ignition hot, terminating in cab console - with 6 foot tails (hot and ground).	1		
CM, Power Source, 12 VDC, 30 Amp (+-), Ignition Hot Termination: Behind Passenger seat with 6 ft coiled wire	2		
CM, Power Source, 12VDC, 40A, Constant Hot (1) Install a 40Amp Power and ground wired to a Buss bar inside the center console (1) Install a 40Amp Power and ground wired IGNITION hot to a Buss bar inside the center console	2		



DESCRIPTION	QTY		
CM, Buss Bar Assembly (+/-), 5 Position, (1) Power and (1) Ground <b>Location: Center console For 40A power sources</b>	2		
<b>VOLTMETER</b>			
CM, Voltmeter, Smart with Alarm, Audio/Visual With additional light on Cab Console for visual alarm.	1		
<b>BATTERY SYSTEM</b>			
CM, Battery Switch, RelayPlex Electronic w/5 min Timer, Ford T1, Batt under Hood <b>- Activated thru OEM ignition switch, timer function upon ignition "off".</b> <b>- Momentary rocker switch, on driver's side of cab console, to function as timer shutoff and also reactivate timer.</b> <b>- (2) OEM batteries</b> <b>- ONLY Module power is turned on/off.</b> <b>- Chassis power is NOT turned off.</b>	1		
<b>BATTERY CHARGER</b> <b>12VDC OUTLETS</b>			
CM, Power Outlet, Power Point Style, (2), (1) Action Area (1) RF ALS Cabinet <b>on standard 20-amp ignition hot circuit.</b> <b>- (1) outlet in action area</b> <b>- (1) in RF Cabinet "U8", wall #2, upper right down low in walkthrough area facing C/S</b>	1		
CM, Power Outlet, Power Point Style, Each <b>Ignition sw hot</b> <b>(1) Above squad bench, 18" up from the top deck of the squad bench, 3" over from the edge of the foot of squad bench wall.</b> <b>(1) in RF Cabinet L8, wall #2, upper right</b> <b>(1) battery hot front bulkhead wall</b>	3		
CM, Power Outlet, Kussmaul, USB Dual Port, 5VDC, 4.8 Amp, switch panel <b>Ignition Hot</b> <b>(1) Located in the cab switch panel passenger side.</b> <b>(1) located top left of console face.</b> <b>(1) located top right of console face.</b>	3		
CM, Power Outlet, Kussmaul, USB Dual Port, 5VDC, 4.8 Amp, switch panel, Addition <b>Location in the Action area outlet panel.</b> <b>Ignition Hot</b>	1		
<b>FRONT CONSOLE</b>			
CM, Console, Drivers Switch & Radio, Center, Aluminum, Black, Type1 Ford <b>Black polyurethane coated .090 Aluminum</b>	1		
CM, Single Blank Panel	1		
CM, 9" deep Glove Box Panel	1		
CM, Cup Holder Panel (No Handle Notch)	1		
<b>ATTENDANT CONTROL PANEL</b>			
CM, Action Area Switch Panel, Eaton Esport switches, Relocate CS Wall	1		

DESCRIPTION	QTY		
CM, Switch, Momentary, Rocker, (1) - Wired To:(1) Right rear entry door, interior lower panel, in top left corner. For power door locks.	1		
<b>SIREN ELECTRONIC - CONTROL HEADS / AMPS</b>			
CM, Siren Electronic, Whelen, WS-295-SLSA1	1		
<b>SIREN SPEAKERS</b>			
CM, Siren Speakers, Cast SAD/PSAD3827-20FSD-1, F-Series 2020, Std Thru Front Bumper	1		
CM, Switch, Siren/Horn Thru Horn Ring	1		
<b>BACK-UP ALARMS</b>			
CM, Back-Up Alarm, No Cutoff Switch	1		
CM, Switch, Emergency Master, Non Sequenced	1		
CM, Beacon Prewire, Ignition Hot to Rearmost Streetside dome No switch Module roof, centered 16" inboard from rear of module, Beacon will be on anytime Ignition is on and unit is in gear.	1		
<b>WARNING LIGHT FLASHERS</b>			
Relay Plex Flash Pattern- Quad Flash 75 - Per KKK			
<b>WARNING LIGHTS</b>			
<b>LED Series - 900 (Flange Separate)</b>			
CM, Light, Whelen 900 LED, Red, Clear Lens, 90RR5SCR, External Flasher (4) 2 each side standard location Pri/Sec (2) Rear upper outer corner's Pri/Sec (2) Front 1 each side of center white light (Cool bar) Pri only (2) front of module angled ends of cool bar Pri only (2)Rear just below corner lights ILO rear window lights !! Pri/Sec W/Brake override	12		
CM, Light, Whelen 900 LED, Amber, Clear Lens, 90AA5SCR, External Flasher On center rear Pri/Sec	1		
CM, Light, Whelen 900 LED, Clear, 90CC5SCR, External Flasher On center front cool bar Primary only	1		
CM, Flange, Super 900 LED, #90FLANGC	14		
<b>LED Series - 700 (Flange Separate)</b>			
CM, Light, Whelen 700 LED, Red, Clear Lens, 70R02SCR Mounted Front Upper Outer corners of Mod stacked Streetside (2)Pri/Sec Curbside (2)Pri/Sec	4		
CM, Flange, Whelen, For 7E lights (1), Mods For 7 Series Lights	4		
CM, Light, Whelen, LINZ6R, LED-Red, with chrome flanges (2) as grille lights and	4		

DESCRIPTION	QTY		
(1)Front Fender Warning - Intersectors - LH Side			
(1)Front Fender Warning - Intersectors - RH Side.			
wired thru RelaPlex per elec. eng.			
<b>EXTERIOR AUTOMOTIVE LIGHTING</b>			
CM, Taillight Pkg, Whelen, LED Stop/Tail, Turn & LED Backup, w/WC logo	1		
- Brake- Steady Burn			
- Turn Arrow – sequential arrow			
- Replace backup with 700 LED			
<b>ICC/MARKER LIGHTS</b>			
CM, Light, Red, 2", Marker, LED, Each	2		
(2) in sides of bumper as running lights and Flash with turn..			
CM, Marker/Clearance Lights, Red, LED	3		
(3) On rear as clearance lights.			
CM, Light, Clearance, Amber LED	3		
(3) On Front of module as clearance lights.			
CM, Corner Cap Lts, Multi, LED, (2) Amber (2) Red w/Flashers	1		
- High intensity flashers;Primary/Secondary- As marker lights with headlights			
<b>FLOOD AND LOAD SYSTEMS</b>			
CM, Light, LED, Whelen, Clear, #9SC0ENZR, 24 LED, (1) w/ Chrome Flange	6		
(2) each side as scene lights			
(2) on rear as load lights			
CM, Scene Lights, C/S, Activated with C/S Door Master Hot.	1		
<b>11 - INTERIOR LIGHTING</b>			
CM, Dome Lights, LED, Whelen,White Flange,(3)S/S,(3)C/S, CM+	1		
Three (3) street side in liner and three (3) curbside in liner equally spaced			
Each side controlled by separate switch in action area standard. High/Off/Low			
NOTE: NO VISABLE FASTENERS OR HOLES.			
CM, Timer, Momentary Switch, 15 Minute, Constant Hot Mount switch on C/S wall at the head of the squad bench in the standard location. Switch to allow activation and also deactivation. Wire to street side dome lights in liner on high.	1		
WC, No Lighting Recessed into Trough Cover	1		
<b>SPOTLIGHTS / HANDHELD LIGHTS</b>			
CM, Handheld Spotlight, Novatech, Nighthawk 2000, 100,000 CP	1		
<b>ATTENDANT LIGHT</b>			
CM, Light, Intertek ZY-PIR38 12v, LED, In A/A	1		
<b>SHORELINE INLET</b>			
CM, Super Auto Eject, 20A, White Cover above comp "#2"	1		

DESCRIPTION	QTY		
<b>OUTLETS - 125VAC</b>			
CM, Outlets, 125 VAC, Duplex, (1) Action Wall, (1) Right Front Cabinet	1		
- (1) outlet in action area			
- (1) outlet in the RF Cabinet "U8", wall #2, upper right.			
CM, Outlet, 125 VAC, Duplex, Additional, Each	3		
(1) Interior CS above foot end of squad bench mounted approx. 14"			
up and over 3" from rear wall.			
(1) telemetry area, wall 2 near wall 1, down low			
(1) Per Eng design, CAB SIDE, bulkhead cabinet, below crawl through window behind pass seat.			
<b>BLOCKHEATERS</b>			
Block Heater - With OEM Plug	1		
This option does not include a switch. (STANDARD).			
CM, Inverter/Charger, Vanner LifeSine	1		
Mounted on compt. #2 ceiling			
CM, Exhaust Fan, Single 12V Blower with "clamshell" vent on exterior rear of unit.	1		
<b>CITIMEDIC HVAC SYSTEM</b>			
CM. Generation III Fiberglass Cool Bar cover	1		
CM, Thermostat, Manual, Wabasto	1		
CM, Heat/AC, F1, Combo, w/Coolbar	1		
with thermostat in action area.			
12vdc External Condenser, in Coolbar mounted on front of module. Painted to match front of module.			
CM, Air Conditioning Face Plate, Brushed Stainless Steel with WC Logo	1		
<b>COT MOUNTING PROVISIONS</b>			
<b>Safety Hooks</b>			
CM, Cot Mount, Stryker, Rear Safety Hook Installed	1		
Ship loose with unit			
<b>Cot Mounts</b>			
CM, Cot Mount, 6370/Single Floor Mount, Not Compliant w/CN 8	1		
Center Mount	1		
Non-Compliance to SAE J3027 Patient Cot Mount Notice	1		
SPECIAL NOTE:			
The Litter Fastener/Anchorage you have selected for this order does not meet the performance requirements of the SAE J3027 Recommended Practice for Ambulance Litter Integrity, Retention and Patient Restraint.			
Section 3.11.6 of KKK-A-1822F as revised July 1,2015 specifically relates to Litter Fasteners and Anchorage and requires the installed fastener for wheeled cots to meet the performance requirements of SAE J3027 Recommended Practice for Ambulance Litter Integrity, Retention and Patient Restraint.			

DESCRIPTION	QTY		
<b>OXYGEN AND AIR SYSTEMS</b>			
CM, O2 Cylinder Wrench, Tethered in oxygen compartment.	1		
CM, Rack, Multiversal, Zico #QR-MV, W/ Straps Fits a M or H cylinder, set MV rack for an M cylinder	1		
CM, Track, Unistrut for Oxygen Rack	1		
CM, Manual, O2 System	1		
CM, O2 Regulator, Preset 50PSI	1		
CM, O2 System, Ohio Style, (2 AA, 1 Vac Port, 1 Liner, 1 C/S)	1		
Ohio style outlets (2) oxygen outlets in action area (1) vacuum port in action area (1) oxygen outlet in liner at head of cot (1) oxygen outlet curbside wall at head of squad bench			
CM, Lexan Flap, w/Hinge	1		
<b>SUCTION SYSTEM</b>			
CM, Suction Pump, SSCOR 90206 mounted in compartment "2"	1		
CM, Suction Holder, SSCOR 23002 with w/Canister Clip & Regulator Conforms to J3043 requirements	1		
WC, Suction Outlet and Container Relocated to Face of A/A in recessed pocket	1		
<b>PAINT AND FINISH</b>			
WC, Wheeled Coach Paint Process	1		
CM, Module Paint, Single Color, OEM White Ford white: FA91:YZ	1		
Cab Paint - Single Color, OEM White	1		
<b>PAINT STRIPING DESIGN</b>			
Paint Belt, None	1		