

## Specification Summary

North Eastern Rescue Vehicles  
Bob Reilly  
10 Dwight Park Drive  
Syracuse, NY

**Contact:** North Eastern Rescue Vehicles, Inc.  
Robert Reilly  
10 Dwight Park Drive  
Syracuse, NY 13209  
UNITED STATES

### Name

**CCL150**



### Specifications

- Aluminum Extruded Body Construction
- CrestCoat Powder Coating Technology
- Aluminum Cabinets
- Multiplex Electrical System
- Flush Mount Windows

## Sales Options by Category

### Base

#### Name/Description

#### Quantity

**TYPE I - CCLP150**

1.00

TYPE I - CCLP150

**72in Interior Headroom**

1.00

72in Interior Headroom

### Chassis

#### Name/Description

#### Quantity

**GM CK3500 chassis cab 4x4 gas**

1.00

Chevrolet 3500HD Gas Chassis Cab 4X4Engine VORTEC SFI 6.6L Gas V8Wheelbase 171"  
(4318 mm)GVWR (Gross vehicle weight rating) 14,000 Lbs / 6,350 Kg

<b>Anti-theft</b>	1.00
Anti-theft security system	
<b>High Idle</b>	1.00
High Idle system	
<b>OEM chassis mirrors</b>	1.00
OEM chassis mirrors	
<b>Wheel alignment</b>	1.00
Wheel alignment completed at the factory	
<b>Running Boards</b>	1.00
Diamond-plate aluminum running boards with grip strut	
<b>Hidden front grille door unlock switch</b>	1.00
Hidden front grille door unlock switch	

### **Drivers Compartment**

<i>Name/Description</i>	<i>Quantity</i>
<b>Control center with pictogram labelled switches</b>	1.00
Control center with switches and LED backlit pictograms on console	
<b>Manual adjustment seat</b>	1.00
OEM manually adjustable chassis seats.	
<b>Talk-through with sliding window</b>	1.00
Cab to module talk-through opening with sliding window	
<b>Handheld LED spotlight</b>	1.00
Handheld LED 2,000 lumens spotlight with trigger type switch	
<b>Chassis voltmeter and conversion voltmeter</b>	1.00
OEM chassis voltmeter.Digital conversion voltmeter on driver's console.	
<b>Patient status indicator lights</b>	1.00
Patient status indicator lights (Red/Yellow/Green) on driver's console	
<b>Ram mount console</b>	1.00
Ram mount console	
<b>Door indicator light</b>	1.00
"Door ajar" and "Compartment" indicator light on driver's console	
<b>Two USB charging outlets</b>	1.00
Two USB charging outlets on driver's console	
<b>No floor mount console</b>	1.00
No floor mount console	
<b>Passenger reading light</b>	1.00
Ceiling mount red/white LED reading light centered over passenger seat	

### **Conversion**

<i>Name/Description</i>	<i>Quantity</i>
<b>C1 Compartment, ALS Access and Battery Compartment</b>	1.00
C1 Compartment - ALS inside/outside access with a sealed battery storage area	
<b>C2 Side Entrance Door</b>	1.00
C2 - Side entrance door with tinted flush mount window	
<b>Dual step entry with step well light</b>	1.00
Two-step interior access with LED step well light	
<b>C3 Compartment, Equipment Storage</b>	1.00
Open storage in C3 Compartment	
<b>C3 - Backboard storage</b>	1.00
Dual backboard storage with straps, two adjustable shelves for equipment bags, and stair chair storage in C3 Compartment.	
<b>S1 Compartment - Main Oxygen Storage</b>	1.00
Main oxygen storage in S1 Compartment	

<b>S2 Compartment - ECC</b>	1.00
Electrical Control Center (ECC) with lower equipment storage in S2 Compartment	
<b>ECC cover</b>	1.00
Aluminum panel in ECC compartment to cover and protect electrical from water and debris	
<b>S3 Compartment, Outside access closed off</b>	1.00
Equipment storage with outside access closed off in S3 compartment	
<b>50/50 Rear doors</b>	1.00
50/50 Split rear entry doors with flush mounted tinted windows	
<b>Black rubber fenderettes</b>	1.00
Flexible black rubber fenderettes over rear wheels	
<b>Rear kick plate with no text</b>	1.00
Rear kick plate with no text	
<b>Aluminum rub-rails on each side</b>	1.00
Aluminum rub-rails on each side of conversion	
<b>Undercoating protection</b>	1.00
Undercoating protection	
<b>Rear mudguard</b>	1.00
Rear mudguard	
<b>Rear bumper underbody</b>	1.00
Rear bumper underbody	
<b>Module front corner stone guard</b>	1.00
Module front corner stone guard aluminum checker-plate protection	
<b>Flush license plate with LED light</b>	1.00
Flush license plate with LED light	

### Exterior Lighting

<i>Name/Description</i>	<i>Quantity</i>
<b>Clearance lights</b>	1.00
Clearance lights - Seven amber and seven red LED marker lights	
<b>Two 3/4 inch red LED mid-body side lights at rear</b>	1.00
Two 3/4 inch red LED mid-body side lights at rear to be marker top with turn signal below	
<b>Two red LED brake/tail lights</b>	1.00
Two red LED brake/tail lights	
<b>Two amber LED turn lights</b>	1.00
Two amber LED turn lights	
<b>Two white LED reverse lights</b>	1.00
Two white LED reverse lights	

### Emergency Systems

<i>Name/Description</i>	<i>Quantity</i>
<b>Colored lens</b>	1.00
Emergency lights to have colored lenses	
<b>Five Whelen 900-Series lights</b>	1.00
Five Whelen 900-Series lights (Red / Red / White \ Red \ Red) on front of conversion	
<b>Two Whelen 700-Series red lights, one each side</b>	1.00
Two Whelen 700-Series red intersection lights, one each side of chassis	
<b>Two Whelen LIN6 Series red lights</b>	1.00
Two Whelen LIN6 Series red lights	
<b>Four Whelen 900-Series red lights (two each side)</b>	1.00
Four Whelen 900-Series red lights (two on each side of conversion)	

<b>Mid Body 700 Series above rear wheel</b>	1.00
Two Whelen 700-Series red lights above rear wheel, one each side	
<b>Four Whelen 900-series halogen scene lights</b>	1.00
Four Whelen 900-series halogen scene lights (two on each side of conversion)	
<b>Two Whelen 900-Series and one 700-Series lights</b>	1.00
Two Whelen 900-Series and one 700-Series lights (Red / Amber \ Red) on rear of conversion	
<b>Two Whelen 600-Series Halogen load lights</b>	1.00
Two Whelen 600-Series Halogen load lights on rear of conversion	
<b>Two 9x7 red lights at window height on rear</b>	1.00
Two 9x7 red lights at window height on rear of conversion	
<b>Siren amplifiers (100 watt)</b>	1.00
100 Watt Siren amplifier with 4 tones and public address (P/A) microphone	
<b>Two siren speakers in front bumper</b>	1.00
Two siren speakers in front bumper Type 1	
<b>Interior Curbside Configuration</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Two (2) position squad bench, 6-point harness</b>	1.00
Two position squad bench with 6-point harness system. Provides ability for second patient transport using backboard. Includes recessed waste and sharps container at head of squad bench.	
<b>Curbside locking sharps container</b>	1.00
Curbside locking sharps container.	
<b>Curbside overhead aluminum cabinet</b>	1.00
Overhead aluminum cabinet above curbside seating	
<b>ALS Compartment</b>	1.00
Front ALS compartment with two adjustable shelves	
<b>Drug cabinet</b>	1.00
Drug cabinet above ALS compartment	
<b>Interior Streetside Configuration</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>CPR seat with 6-point harness system</b>	1.00
CPR seat with 6-point harness system	
<b>Fixed frames</b>	1.00
Fixed frames with sliding polycarbonate doors	
<b>Aluminum countertop</b>	1.00
Aluminum countertop - Powder coated	
<b>Attendant Seat</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Child safety device</b>	1.00
Rear-facing EVS seamless vinyl seat with child safety device and 3-point seatbelt	
<b>Box Base with front/rear slider</b>	1.00
Box Base with front/rear slider	
<b>Cot Configuration</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Ferno 175-3 single floor mount</b>	1.00
Ferno 175-3 single floor mount with yellow safety stop block	
<b>Center mount cot configuration</b>	1.00
Center mount cot configuration	
<b>Oxygen</b>	

<i>Name/Description</i>	<i>Quantity</i>
<b>Quick disconnect style outlet</b>	1.00
Quick disconnect style outlet	
<b>Universal vertical holder</b>	1.00
Universal vertical holder for oxygen cylinder	
<b>Cylinder changing wrench</b>	1.00
Cylinder changing wrench with footman loop assembly in oxygen compartment	
<b>Manual oxygen regulator (50PSI)</b>	1.00
Manual oxygen regulator (50PSI)	
<b>One oxygen outlet in Action Area</b>	1.00
One oxygen outlet in Action Area	
<b>One ceiling mounted oxygen outlet</b>	1.00
One ceiling mounted oxygen outlet	
<b>One oxygen outlet on curbside wall</b>	1.00
One oxygen outlet on curbside wall	

### **Electrical**

<i>Name/Description</i>	<i>Quantity</i>
<b>Multiplex system</b>	1.00
Multiplex electrical system using toggle switches with LED backlit pictogram.	
<b>Rear speaker volume control</b>	1.00
Rear speaker volume control at Action Area	
<b>Temperature control with automatic setting</b>	1.00
Temperature control with automatic setting at Action Area.	
<b>Patient status indicator lights</b>	1.00
Patient status indicator lights (Red/Yellow/Green) at Action Area.	
<b>On/off LED reading light</b>	1.00
On/off LED reading light above Action Area.	
<b>Four antenna ports with pre-wiring</b>	1.00
Four antenna ports with pre-wiring for antenna RG 58 A/U	
<b>Two OEM batteries</b>	1.00
Two OEM batteries	
<b>Back up alarm</b>	1.00
Back-up alarm (97db)	
<b>Round LED compartment lighting</b>	1.00
Round LED compartment lighting	
<b>Six LED dome lights</b>	1.00
Six LED dome lights with multiple intensity settings	
<b>Xantrex Freedom XC pure sine-wave inverter/charger</b>	1.00
Xantrex Freedom XC pure sine-wave inverter/charger	
<b>Auto Eject - Yellow 20 amps</b>	1.00
Auto-eject shoreline outlet - 120V 20 amp assembly with a yellow waterproof cover	
<b>Shoreline light</b>	1.00
Indicator light above the shoreline plug to show power connection	
<b>1 120V GFCI outlet in Action Area</b>	1.00
One Hospital-grade 120 VAC GFCI dual outlet with indicator light in Action Area	
<b>1 120V outlet in upper ALS area</b>	1.00
One Hospital-grade 120 VAC dual outlet with indicator light in upper ALS area	
<b>One 12 VDC outlet in lower ALS area</b>	1.00
One 12 VDC outlet in lower ALS area	
<b>One 12 VDC outlet in Action area</b>	1.00
One 12 VDC outlet in Action area	

<b>Camera monitor in cab</b>	1.00
Camera monitor in cab	
<b>Back-up camera</b>	1.00
Back-up camera	
<b>Rico RS4X disposable suction system</b>	1.00
Rico RS4X disposable suction system in Action Area	
<b>HVAC</b>	
<b>Name/Description</b>	<b>Quantity</b>
<b>Combo heat and AC</b>	1.00
Combo heat and air conditioning with exhaust fan for contaminated air	
<b>Accessories</b>	
<b>Name/Description</b>	<b>Quantity</b>
<b>Analog clock above rear entry doors</b>	1.00
Analog clock mounted above rear entry doors	
<b>L-shaped yellow grab bar on side entry door</b>	1.00
L-shaped yellow grab bar on side entry door	
<b>L-shaped yellow grab bars on rear entry doors</b>	1.00
L-shaped yellow grab bars on rear entry doors	
<b>One 61in ceiling mounted grab rail</b>	1.00
One 61in ceiling mounted yellow grab rail	
<b>One 61in ceiling mounted grab rail (qty 2 total)</b>	1.00
One additional 61 inch ceiling mounted yellow grab rail (qty 2 total)	
<b>Four clip style IV hangers with strap</b>	1.00
Four clip style IV hangers with strap (2 curbside wall, 2 streetside wall)	
<b>Spare plastic trash liners</b>	1.00
Twelve spare plastic trash liners	
<b>Finish and Trim</b>	
<b>Name/Description</b>	<b>Quantity</b>
<b>Interior powdercoated white</b>	1.00
Cabinets, wall panels and ceiling are white powder-coated aluminum	
<b>Black upholstery</b>	1.00
Black vinyl upholstery with yellow head bolster pads on entry doors	
<b>Floor : Slip resistant, rolled-up 5 in. (127mm)</b>	1.00
Floor : Slip resistant, rolled-up 5 in. (127mm)	
<b>Lonplate II Midnight #443TXM</b>	1.00
Lonplate II Midnight #443TXM flooring	
<b>Clear anti-slip spray</b>	1.00
Clear anti-slip spray applied to side entry steps	
<b>Paint and Graphics</b>	
<b>Name/Description</b>	<b>Quantity</b>
<b>Powdercoat module white</b>	1.00
Powdercoat entire module white to match the chassis	