



# Specification Summary

North Eastern Rescue Vehicles

10 Dwight Park Drive  
Syracuse, NY 13209

North Eastern Rescue Vehicles, Inc.

10 Dwight Park Drive  
Syracuse, NY 13209  
UNITED STATES

## Name

Type II - TS



## Specifications

Overall Length 236" (599 cm)  
Overall Width 98" (249 cm)  
Overall Height 103" (262 cm)\*  
Headroom 69" (175 cm)  
Wheelbase 148" (376 cm)  
Payload Capacity Up to 2,500 lbs (1134 kg)

\*Total height of vehicle may differ according to chassis and suspension

## Sales Options by Category

### 10-Base (BAS)

Name/Description	Quantity
TYPE II - TS TYPE II - TS	1.00
Type II - Van Type II - Van	1.00

### 11-Chassis (CH\*)

Name/Description	Quantity
Conversion Ford T250 Van Conversion Ford T250 Van	1.00
Ford Transit T250 Gas Van AWD Ford Transit T250 Gas Van AWD 3,5L EcoBoost® V6 Gasoline Engine	1.00



Mid Height Roof  
Wheelbase 148" (3760 mm)

**16-Emergency and Working Lights (EWL)**

<i>Name/Description</i>	<i>Quantity</i>
<b>Demers T2 Aero Cab Riser TS 2RR-2C3RC-2RR</b> Demers Aerodynamic Cab Riser (500 series), 2RR-2C3RC-2RR	1.00
<b>Four (4) LED in grille (LINZ6) WIG WAG</b> Four (4) lights in front grille with Wig Wag flash pattern. LINZ6 series (4 x 2) LED lights. (Standard setup includes (2) red and (2) clear)	1.00
<b>Intersection Lights, (2) LED (700)</b> Two (2) intersection lights. Whelen 700 series (7 x 3) LED lights. (Standard setup contains red lighting)	1.00
<b>Emergency Lights, (2) LED, Inter. Side Mount (700)</b> Two (2) emergency lights, intermediate side mount. Whelen 700 series (7 x 3) LED lights. (Standard setup contains red lighting)	1.00
<b>Four (4) LED lateral emergency lights (600)</b> Four (4) LED lateral emergency lights (two (2) on each side, 600 series 6 X 4) (Standard setup contains red lighting)	1.00
<b>Scene Lights, Four (4), Clear LED, (600)</b> Four (4) lateral LED scene lights (two (2) on each side) 600 series 4 x 6	1.00
<b>Rear Spoiler TS 1R-1W-1A-1W-1R</b> Demers aerodynamic rear spoiler with 1 red / 1 white / 1 amber / 1 white / 1 red (500 series 5 X 1, perimeter lights 8 X 2)	1.00
<b>Two (2) Rear LED lights (700 series 7 X 3)</b> Two (2) Rear LED lights (700 series 7 X 3) (Standard setup contains red lighting)	1.00
<b>AMBER ION or equivalent between Spoiler Lights IATS</b> VTX609 Omni Direction Lighthouse, Red, Blue, amber or White, 9" cable. Quoted a total of (2) Whelen Vertex VTX609 rear warning lights: BLUE / SCENE / RED / SCENE / RED	1.00

**17-Audible Warning System (WRN)**

<i>Name/Description</i>	<i>Quantity</i>
<b>Back-Up Alarm</b> Back up alarm (97dB) with override switch.	1.00
<b>Whelen 295SLS Hands-Free Siren</b> Whelen model 295HFSA1 siren amplifier with 17 Scan-Lock™ siren tones.	1.00
<b>Whelen SA315 Series Speakers</b> Whelen SA315 series speakers is a compact speaker meeting SAE Class A requirements when paired with Whelen 100 watt siren amplifier.	1.00

**18-Exterior Vehicle features (VFT)**

<i>Name/Description</i>	<i>Quantity</i>
<b>Front cab mud guards</b> Front cab mud guard flaps ford	1.00
<b>OEM exterior mirrors</b> Keep OEM exterior mirrors	1.00
<b>Undercoating Protection</b> Undercoating protection for module and chassis.	1.00
<b>Van Anti-skid rear steps</b> Van Anti-skid rear steps.	1.00



<b>Van Lateral Steps, Anti-Skid Material &amp; Mud Guards</b>	1.00
Anti-skid lateral steps includes: mud guards	

### 19-Convenience (CNV)

<i>Name/Description</i>	<i>Quantity</i>
<b>Demers Fast Idle</b> Demers fast idle is generated by the multiplex module, it allows fast charging of the batteries by the engine when specific conditions are met.	1.00
<b>Anti-Theft System</b> The anti-theft allows leaving the vehicle without keys and the engine running to keep the vehicle at the ideal operating temperature. It protects against theft by turning off the engine if the vehicle moves.	1.00

### 22-Drivers Compartment (CAB)

<i>Name/Description</i>	<i>Quantity</i>
<b>Spotlight in Front Cab, Hand-Held, with Bracket</b> Hand-held spotlight, 2000 lumens, with trigger-type switch and bracket.	1.00
<b>Fire extinguisher (5 lbs) ABC with bracket</b> Fire extinguisher (5 lbs) ABC with heavy duty bracket	1.00
<b>Control center with 4.3in touch screen in the lower dashboard - Type II</b> Control center with 4.3in touch screen in the lower dashboard - Type II	1.00
<b>Cab headliner with OEM reading lights</b> Sprinter Type 2 ceiling with access flaps	1.00
<b>Goose neck reading lamp</b> Goose neck reading lamp on front console.	1.00
<b>Strap behind passenger seat to secure Model 12 litter.</b> -strap behind passenger seat to secure Model 12 litter.	1.00

### 23-Curbside Configuration (CRB)

<i>Name/Description</i>	<i>Quantity</i>
<b>Mount for Cardiac monitor at head of squad bench</b> Mount for Cardiac monitor at head of squad bench	1.00
<b>Safety Net</b> Safety net at the head of the curbside configuration, by the side entry door (C2).	1.00
<b>Full Length Seat Backrest</b> Single full length molded seat backrest	1.00
<b>Single full length molded seat cushion</b> Full length molded seat cushion (Medium : 45 - 50 inches )	1.00
<b>Seating for two (2) passenger, 6 pts safety belt</b> Seating for two (2) passenger, 6 pts safety belt	1.00

### 24-Streetside Configuration (STR)

<i>Name/Description</i>	<i>Quantity</i>
<b>Flip-Up Door, Clear Sliding Window</b> Aluminum flip-up frames, self latching for easy restocking of cabinets. Polycarbonate clear sliding windows.	2.00
<b>Reeve's stretcher compartment</b> Compartment and flip up door (Reeve's stretcher compartment)	1.00
<b>Polycarbonate Clear Sliding Windows</b> Polycarbonate clear sliding windows. Type 2	4.00
<b>Lower Medical Cabinet, Full storage for TS</b> Medical cabinet with long counter top and full storage area	1.00

### 25-Forward Bulkhead (FWB)



<i>Name/Description</i>	<i>Quantity</i>
<b>Pass-through sliding window</b> Pass-through sliding window on front division for communication with cab. Type 2	1.00
<b>Upper front partition with retaining straps</b> Upper front partition with retaining straps in front TS ALS compartment	1.00
<b>Right side division TS</b> Right side division TS, Stair chair location and fixed shelf	1.00
<b>Two (2) see-through windows, stainless lock</b> Two (2) angled doors with see through windows and stainless steel lockable handle - lower front partition	1.00
<b>26-Attendant Seat (AST)</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>EVS 1860 3Pts Vac-Formed Seamless ChildSeat, Fixed</b> EVS 1860 3Pts Vac-Formed Seamless Child Seat, Fixed Base	1.00
<b>27-Cot Configuration (COT)</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Floor Plate for Stryker Performance-LOAD</b> Stryker Performance-Load floor plate. No cot fastener included.	1.00
<b>Wheel guide for cot location</b> Cot wheel guides for left side location	1.00
<b>Left side floor mount cot configuration</b> Left side floor mount cot configuration Type 2	1.00
<b>28-Rear Control Panel (CAR)</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>4.3in color touch screen console - Type II</b> 4.3in color touch screen console - Type II	1.00
<b>29-Oxygen (OXY)</b>	
<i>Name/Description</i>	<i>Quantity</i>
<b>Oxygen Compartment rear curbside</b> Vertical Oxygen Compartment rear curbside Pivoting access door for oxygen tank. (Included)	1.00
<b>Oxygen Outlets, Three (3)</b> Three (3) oxygen outlet, two (2) in ECC, one (1) on curbside	1.00
<b>Oxygen Outlet, Quick-Connect</b> Quick-connect style oxygen outlet.	3.00
<b>Oxygen Regulator, Manual, 50 PSI</b> Manual oxygen regulator (50PSI).	1.00
<b>"D-size" Portable oxy storage (2) in squad bench</b> "D-size" Portable oxygen cylinder storage (2) located in squad bench	1.00
<b>Universal vert oxygen cylinder holder "K" or "M"</b> Universal vertical holder for main oxygen cylinder type "K" or "M"	1.00
<b>Main oxygen strap</b> Main oxygen strap needs to be installed with buckle toward rear of vehicle.	1.00
<b>Vacuum outlet QD Puritan with yellow 5/16" hose 4 ft long</b> Can't find option for this anymore in CPQ: Vacuum outlet QD Puritan with yellow 5/16" hose 4 ft long (SUC-OUT-11)	1.00
<b>31-Suction (SUC)</b>	
<i>Name/Description</i>	<i>Quantity</i>



<b>Suction System location in ECC</b>	1.00
Main suction system is located in front streetside action area.	
<b>Thomas high flow vacuum pump</b>	1.00
Thomas high flow vacuum pump	
<b>Vacuum regulator with disposable canister</b>	1.00
Vacuum regulator with disposable canister	

### 32-Electrical System (ELE)

<i>Name/Description</i>	<i>Quantity</i>
<b>Power Inverter, Xantrex Freedom, True Sine, 1000W</b>	1.00
The inverter/charger provides AC power using the DC power from the conversion battery bank. Recharge all battery banks and power all 120 volts AC outlets when the external shoreline is connected.	
<b>Super Auto Eject Power Inlet, 15 Amps, Yellow</b>	1.00
Kusmaull 120 Volts AC, 15 AmpsAutomatically disconnects shorelineCompletely sealedYellow coverIndicator light	
<b>Electrical Outlet, 120V AC with Indicator</b>	1.00
120V AC hospital-grade electrical outlets with indicator.	
<b>Add 120V AC Duplex outlet with indicator</b>	1.00
Additional 120V AC Duplex outlet with indicator. Details and location are as follows: 120V outlet in cabinet below ECC; on SS wall toward front corner.	
<b>Electrical Outlet, 12V DC 20 amp with Indicator</b>	1.00
12V DC, 20 amp Duplex electrical outlets.	
<b>Two (2) OEM batteries</b>	1.00
Two (2) OEM batteries for Type II vehicles.	
<b>Management System (DEMS) – MMC system.</b>	1.00
Management System (DEMS) – MMC system.	
<b>Pre-wire 12v 6' coiled beneath passenger seat</b>	1.00
For CUSTOMER INSTALLED computer docking station..."14 gauge power line, end taped off for us to install the docking station	

### 33-Communication System (COM)

<i>Name/Description</i>	<i>Quantity</i>
<b>Pre-Wiring for 2-Way Radio, Two (2) Antenna Cables</b>	1.00
Wiring preparation for two-way radio, with two (2) antenna cables.(routed from front cab to radio communication compartment)	
<b>Radio Communications Compartment</b>	1.00
Radio communications compartment universal board, Bussmann blade-type fuse panels, and harness to power the radio communication devices.(12V battery feed, ground, ignition).	
<b>Data Recorder Available Signals</b>	1.00
Data recorder available signals through a universal connector in the electrical compartment.	

### 34-HVAC (CVC)

<i>Name/Description</i>	<i>Quantity</i>
<b>Ducted combo AC/heating unit tie-in to OEM</b>	1.00
Ducted combo air conditioning / heating unit tie-in to OEM on curbside	
<b>Exhaust fan single</b>	1.00
One (1) exhaust fan for contaminated air. Activated by front control interface or rear console switch.	

### 35-Interior Lights (ILG)

<i>Name/Description</i>	<i>Quantity</i>
-------------------------	-----------------



<b>LED Dome Lights, Adjustable, Dig. Timer</b>	7.00
The ceiling lights have four (4) different intensities. Each time the ceiling lights button is pushed, the intensity increases, until maximum intensity is reached.	

**36-Grab Handles (GBR)**

<i>Name/Description</i>	<i>Quantity</i>
<b>Grab Bars Color, Yellow</b> Color of selected grab bars is Yellow.	1.00
<b>Two (2) rear door mounted soft grab bar, 7"</b> Two (2) door mounted grab bars, 7", inside of rear doors (A1 and A2).	1.00
<b>Embarking Grab Bars, 12"</b> Two (2) entry grab bars, 12" each, mounted inside the patient compartment. One (1) near the curbside entry door, and one (1) near the R2 rear entry door.	1.00
<b>One (1) ceiling mounted grab rail, 60"</b> One (1) ceiling mounted grab rail, 60"	1.00

**37-Finish and Trim (FNS)**

<i>Name/Description</i>	<i>Quantity</i>
<b>Rear doors trims</b> Rear Exterior Door finish TS.	1.00
<b>Lonseal, Lonplate II, Gun metal</b> Lonseal, Lonplate II, Gun Metal floor covering.	1.00
<b>Ambassador Grey Upholstery</b> Ambassador grey vinyl upholstery for seat and padding covering.	1.00
<b>Black Upholstery</b> Black vinyl upholstery for seat and padding covering.	1.00
<b>Safety Yellow Upholstery</b> Yellow vinyl upholstery for safety exit padding covering.	1.00
<b>Insulation ethafoam between chassis and floor</b> Insulation (0,125 ethafoam) between chassis and floor boards.	1.00
<b>Plywood wood flooring</b> Exterior grade plywood, 0,625 inches thick.	1.00
<b>Fiberglass Ceiling</b> Fiberglass ceiling in Patient Compartment.	1.00
<b>General Vehicle Identification</b> Vehicle general labels identification.	1.00

**38-Functionality (FCT)**

<i>Name/Description</i>	<i>Quantity</i>
<b>Fire extinguisher ABC with heavy duty bracket</b> Fire extinguisher (5 lbs) ABC with heavy duty bracket in patient compartment	1.00
<b>Sharps Container in Front Action Area</b> Sharps disposal container with bracket installed in the front action area (ECC).	1.00
<b>Two (2) recessed/flexible IV hooks in ceiling</b> Two (2) recessed/flexible IV hooks in ceiling	1.00
<b>Trash Container, Flip-Down, Hands-Free</b> Trash container bracket in curbside flip-down container.	1.00
<b>Two (2) recessed radio speakers</b> Two (2) recessed radio speakers.	1.00