



QUOTATION

North Eastern Rescue Vehicles, Inc.

WO#: 694967

DESCRIPTION		QTY		
INFORMATION		1		
> State Contract		1		
Manufacturer Certified ISO 9001		1		
WARRANTY				
WC, Warranty, Conversion, 12 Month		1		
WC, Warranty, Paint, 60 month Prorated, Standard		1		
WC, Warranty, Structural, 20 Years, Std., Mods		1		
WC, Warranty, Limited Electrical		1		
WC, Warranty, Cabinet Construction		1		
CERTIFICATIONS REQUIRED				
< This unit built in accordance with KKK-A-1822-F in effect on the date of order with exceptions as noted herein.		1		
< WC, This unit built in accordance with KKK-A-1822F CN 10 Cabinet Requirements This unit as specified meets all requirements of KKK-A1822-F Change notice 10.		1		
All cabinets shall be labeled as to their capacity Rating.				
01- CHASSIS REQUIREMENTS				
FORD CHASSIS				
S < > CM, 2027 Ford E350, 7.3L, Gasoline,Cutaway, 138"WB Auto throttle OEM Ford (1) OEM Alternator Includes 2nd battery OEM Cab Headliner Vinyl		1		
Domestic Chassis		1		
SUSPENSION				
Rear Suspension, OEM Springs		1		
HIGH IDLE				
High Idle Controls, OEM		1		
FRONT END ALIGNMENT				
Front End Alignment, None- QC Check -Standard		1		
OUTSIDE REAR VIEW MIRRORS				
Mirrors, Sail Mount, OEM Mirrors		1		
WHEEL COVERS				
< CM, Wheel Covers, Phoenix #NF12, Installed,E-Series with Air Max Valve Extenders		1		

DESCRIPTION		QTY		
BASE CONVERSION				
	CM, Conversion, Type 3, 148 Module, Ford - 23-1	1		
CAB EXTENSION				
<	CM, 8" Cab Extension, Ford, CitiMedic E350 Cab Extension to utilize same flooring as Module floor. ECN # 2096	1		
MODULE BODIES:				
	CM, Interior Headroom, 68 Inches	1		
<	CM, Module, Type 3, 148" Body Length, 90" wide, Duraseam Doors, Cutaway 148" L x 90" W	1		
<	CM, Aisle Space, 49", CityMedic Plus (48-49" actual)	1		
03 - MODULE EXTERIOR				
EXTERIOR MODULE CONSTRUCTION				
>	CM, Stone Guard, Front, Diamond Plate, Type 3, Standard Height	1		
FUEL FILLS & SPLASH PLATE				
	CM, Housing Fuel Fill, Cast, Type III	1		
REAR KICKPLATE				
	CM, Rear Kick plate, Under-Ride Bumper, w/ Tag recess, No lights, CM+	1		
SUB-FLOOR SYSTEM				
	CM, Flooring, 3/4" Marine Grade Plywood, Type 3/7/9	1		
MODULE ENTRANCE				
MODULE DOORS, HANDLES & HOLD OPENS				
<	CM, Duraseam Hinged Doors with Hidden Jambs - Magnetic door switches, Standard	1		
< >	CM, Hold Open Rear Entry Doors, (2) 6" Door Grabber - Installed so doors will open as wide as possible - Mount at Bottom of doors.	1		
	CM, Hold Open, Gas Strut, Curb Side Entry Door, 35#	1		
<	CM, Patient Entry Door Handles, Trimark Black/Chrome Pull Handle w/"Push Button" With Round Push button Emergency release top and bottom of interior door panels.	1		
>	CM, Rear Entry Door Trailing Latch, Side release Paddle	1		
>	CM, Electrical Feed to Required Doors, Spring Protector (Per Door)	7		
POWER DOOR LOCKS				
< >	CM, Power Door Locks, All Module doors (except Batt) Access Doors and Module Compartment doors (except Battery) for electric locks, wiring to CS wall for Switch.	1		
<	CM, Switch, Stealth, for Power Door Locks In grille on passenger's side	1		
< >	CM, Switch, 12VDC, (3) Position Rocker, For Power Door Locks, Additional (1) Right rear entry door, interior lower panel, in top left corner. For power door locks.	1		

DESCRIPTION	QTY		
> CM, Relay Control Circuit, Power Door Locks	1		
> CM, Circuit, OEM Door Lock to activate Mod Doors (Not Dodge)	1		
ENTRY DOOR INNER PANELS			
< > CM, Entry Door Panels, Upper/Lower, S/S	1		
- Durasafe Design			
> CM, Blue/White Center Chevron, w/WC Logo	1		
SIDE DOOR STEP			
CM, Side Entry Step Well, Type III, Aluminum Diamond Plate	1		
CM, Light, Side Entry Step well, LED, 2", Whelen	1		
#TOCACCCR			
WINDOWS			
< CM, Window, Upper, CS/Slider, Rr/Fixed, Privacy Tint, PAN	1		
Curbside window with lower slider section			
Rear windows fixed			
Privacy Tint			
REAR BUMPER AND REAR STEP CONSTRUCTION			
< CM, Rear Bumper, Ford Cutaway, w/ holes for 2" LED Lights	1		
with Gator Grip on flip up step.			
holes in sides of bumper for 2" marker light			
CM, BLACK Polyurethane Coating, Rear Bumper Supports	1		
INSULATION			
< > CM, Insulation, Walls and Ceiling, R11 Fiberglass Batt	1		
There shall be double bubble insulation in the entry and compartment doors.			
RUB RAIL AND FENDER RINGS			
CM, Rub Rails, Skirt Line, Extruded "C" channel (E-one Style), 148"	1		
CM, Tape, Reflective, White, For Extruded Skirt rails	1		
CM, Fender Flare, Black Rubber	1		
SPLASH GUARDS AND RUNNING BOARDS			
CM, Mud Flaps, Rear, w/ Wheeled Coach Logo	1		
CM, Running Boards, Ford Cutaway, w/Gator Grip,	1		
CAB TO MODULE ACCESS			
< CM, Bulkhead Cabinet, Type 3, walk-thru w/8" Cab extension	1		
- with 8" extended cab area			
- With walk thru door			
< CM, Bulkhead, Door, Sliding w/Sliding Window	1		
with sliding Lexan window			
LICENSE PLATE HOLDER			
< CM, License Plate Holder, Cast LP0002, for Under ride Bumper	1		
in rear kick plate, centered			
License holder comes with (2) LED lights.			
EXTERIOR COMPARTMENT CONSTRUCTION			
< CM, Compartments, Std, Floor Drop Down	3		
Compartment #2 - 2.5" drop			
Compartment #4 - 4" drop			
Compartment #6 (5.5" for spare tire)			

DESCRIPTION	QTY		
Drop down floors to have drain hole standard. < CM, Compartments, Sweep out Compartments #1 & #8.5 are standard sweep out < CM, Door Sill Protector, Stainless, All Comps Door Sill Protection - Install Stainless Steel sill protector on lower edge of all door frames to prevent paint damage < > CM, Compartments, Diamond Plate Finish Per Comp Machine stamped louvers located above the floor line for venting. Comp #1, 2, 4, and 6 > CM, Exterior Battery Compartment, Diamond Plate Finish EXTERIOR COMPARTMENT DOORS > CM, Compartment Comp Handle, Trimark, Oval Pull Handle, Black/Chrome COMPARTMENT DOOR HOLD OPEN < CM, Hold Open, Gas Strut, Ext Comp, 30lb. Compartments "#6", "#1", & "#2" < CM, Hold Open, Gas Strut, Comp Door Only, 110 Degree, 30lb, Comp #4 to allow easier access to the Stair chair. < CM, Hold Open, Gas Strut, RF Comp, 30lb #8 COMPARTMENT LIGHTING < CM, Oxygen Light, 3" Surface mount Whelen LED, Clear Mounted in Oxygen Compartment per eng design < CM, Compartment Light, 4" Optronic,#BUL43-CBK, LED, Each Compartment 1 - Access Panel Wall 1 2 - Wall #1 4 - Ceiling 6 - Wall #3 8- Wall #3 in access panel COMPARTMENT #1 - STREETSIDE FWD CM, Compartment #1, 3/4 High, CitiMedic. COMPARTMENT #2 - STREETSIDE FWD WHEELWELL < CM, Compartment #2, Citimedic , Type 3 Mount the inverter on the ceiling of compartment. < CM, Compartment #2, Shelf, ADP, Fixed for Electrical storage Screw in shelf that extends from wall 1 to the recessed suction and wall 2 to flush with the face of the suction dogleg COMPARTMENT #4 - STREETSIDE AFT < CM, Compartment #4, Full Height, Dual Depth, Citimedic - Full height backboard storage on the #4 compartment door. - The upper section is 8" D due to dogleg for interior	2 1 4 1 6 3 1 1 1 6 1 6 1 1 1 1 1		

DESCRIPTION	QTY		
cabinetry. Bottom section is 15" deep.			
Floor drop of 4" for the entire compartment			
< CM, Compartment #4, Strap, Seat Belt Style, Each (1) on comp #4 door for Backboards (1) from wall #1 to Wall #3 about 6" from wall 2 for the Stair chair.	2		
< CM, Compartment #4, Bracket, Backboard Mount on Door Diamond plate "C-style boxes mounted to the door of Comp #4	1		
one at top and bottom to allow backboards or scoop stretcher to be slid in from the outboard side.			
COMPARTMENT #6 - CURBSIDE AFT			
< CM, Compartment #6, Spare Tire, With special Drop pan for spare tire. Do NOT install spare tire bracket.	1		
< CM, Compartment #6, Shelf, Custom, Adjustable, First Shelf wall#1 to wall#3 Mid height	1		
COMPARTMENT #8 - CURBSIDE UPPER FORWARD			
< CM, Compartment #8/8.5, Split Doors, 8" Cab Extension, Upper compartment, with inside /outside access Lower compartment for (2) battery	1		
< CM, Compartment #8, Shelf, Adjustable, First Shelf RF Comp "8"/cabinet "U8" area - centered top to bottom.	1		
< CM, Compartment #8, Shelf, Additional, Adjustable, Each RF Comp "8"/cabinet "L8" area centered top to bottom.	1		
INTERIOR TRIM AND FEATURES			
> CM, Interior Cabinets, Duralite Construction, Wood	1		
< > CM, Cabinet Shelf, Interior, Wood, Adjustable, First shelf Cabinets U4, U6, C6	3		
< CM, Cabinet Shelf, Interior, Wood, Additional, Adjustable Cabinet U4 (2 total)	1		
HEADLINER			
> CM, Headliner, Flat, PVC, Hinged trough cover, Std	1		
FLOORING			
CM, Flooring, Lonplate II, Gunpowder Gray #424TX	1		
< > CM, Flooring, Roll up, 3-4" Approx....., No Toe Kick The roll up is not recessed it is installed on the cabinet wall and Squad bench.	1		
CM, Floor, Thresholds, .063 Aluminum, Painted w/Black Poly-urea coating	1		
GRAB RAILS			

DESCRIPTION		QTY		
Rear Entry Door Grab Handles				
<	CM, Entry Door Grab Handles (3), Custom "L" Shape, 1", Yellow Yellow Powder Coat Finish	1		
Ceiling Grab Rail - Center				
<	CM, Ceiling Grab Rail, Overhead, 84", 1" Diameter Handicap Style, Yellow Yellow Powder Coat Finish	1		
IV FLUID HANGERS				
<	CM, IV Hangers, Perko (1), W/Straps Each (1) CS wall up high centered between seats (1) SS Forward of U3.5	2		
BASEWALL CABINET:				
< >	CM, Cabinet, Base wall, 8" ext, CPR Seat, w/Telemetry Area, Recessed suction Telemetry area to have poured black surface. Cabinet L3.5	1		
<	CM, Cabinet, Street side Upper, 148 Module, w/CPR Seat, 68" HR Cabinet U2, U1 wood door	1		
<	CM, Street side rear, with side seat, 68" HR Cabinet U4 with (2) adjustable shelves Cabinet U3.5	1		
	CM, Tray, A/A, Std Aisle No Bio waste, Poured, Black	1		
CABINET DOORS				
< >	CM, Door, U1 Hinged Wood U1 cabinet will be used as a locking drug cabinet.	1		
	CM, Door, U2 Gray Polycarbonate Slider, CN 10 Compliant	1		
Interior Street side #3 - CPR Seat				
	CM, CPR side seat, Fixed Backrest	1		
<	CM, CPR, Lid, Hinged Flip Up With Trimark Latch	1		
<	CM, Door, U3.5, OHO Top Hinged Gray Polycarbonate (CWTG) CN 10 Compliant CWTG = with gas strut	1		
	CM, Door, L3.5, OHO Bottom Hinged Gray Polycarbonate, (CWBD) CN 10 Comp	1		
	CM, Door, U4, OHO Dual Hinged Gray Polycarbonate (CWDX) CN 10 Compliant	1		
<	CM, CPR Seat, "U" Barrier Bar, Padded, 1.5" SS, Gunmetal Mounted Approx. 12" from the center of the seat to the side of the barrier bar.	1		
	CM, Telemetry Tray, Poured, Black	1		
SQUAD BENCH AREA				
< >	CM, Cabinet, Squad Bench, CM+, w/ Bio waste With Bio waste at the head of the squad bench cabinet.	1		
<	CM, Lid, Squad Bench, Single W/Bio-Waste Lift up lid ONLY over storage area	1		

DESCRIPTION		QTY		
	CM, Squad Bench, Handle, Trimark, STD	1		
<	CM, Strut, Gas, 30 LB, Installed	2		
	CPR Side seat			
	Squad Bench			
	CM, CPR, Handle, Trimark, STD	1		
	CM, Bio-waste Cover, Etched Red Plastic	1		
	SEAT BELTS/ SAFETY NETS			
<	CM, CPR Seat, Seatbelt, Assy, (4 Point), Per4Max, Yellow, (1) Each, CN-8	1		
	Above the lid			
< >	CM, Squad Bench, Seatbelt, Assy, (4 Point) Per4Max, Yellow, (2) Each	1		
	Above the lid			
	On squad bench			
	CM, Patient Restraint Belts, Squad Bench (3)	1		
<	CM, Safety Net, Head of Squad Bench, 2" Straps, Yellow	1		
	attached to floor at head of squad bench, CS wall and overhead liner with removable latches.			
	CURBSIDE REAR			
<	CM, Cabinet, Curbside Rear, In Rear wall, U6,C6 Gray OHO doors, w/two shelves	1		
	(1) adjustable shelf in cabinet U6			
	(1) adjustable shelf in cabinet C6			
	BIOHAZARD-			
>	CM, Glove Butler-Cabinet, (3),Above C/S door	1		
	CURBSIDE RIGHT STACK STORAGE #8			
<	CM, RF ALS, Split Upper/Lower, HVAC at Top	1		
	Upper Cabinet U8			
	Lower Cabinet L8			
	Cabinet - Upper Right Stack U8			
	CM, Doors, RF, U8, Dual Gen III OHO, Polycarbonate Doors, Gray	1		
	CM, Doors, RF, L8, Dual Gen III OHO, Polycarbonate Doors, Gray	1		
	ATTENDANT SEAT			
	CM, Attendant's Seat, EVS 1880,Comfort, Hi-Back Child Safety w/Per4Max	1		
>	CM, Color, Gunmetal, Per4Max Belt, Yellow	1		
>	CM, Door, Diamond Plate, EVS Seat Base, M1 Latch	1		
< >	CM, Attendant's Seat Base, EVS CBS Box Style	1		
	Box opening to be toward CURBSIDE access door			
	INTERIOR COLORS			
	CM, Mica, Dove Gray (Matte)	1		
	UPHOLSTERY			
	CM, Upholstery, Seamless, Gunmetal	1		
>	CM, Backrest Cushion, EVS, Gunmetal, w/ WC Logo, Each	3		
	MISC. INTERIOR OPTIONS			
< >	CM, Marine Hasp, for Padlock Installed	1		
	on U-1 cabinet			
	CABINET KICK PANELS			

DESCRIPTION		QTY		
	CM, Kick plate, Brushed SS, Face of S/B & Base wall, 148 CM	1		
	CABINET LATCHES- INTERIOR			
< >	CM, Latch, M1, 3/4" Material, 2" round, Non Locking, Chrome-CN 10 Certified (1) Sharps/Waste (1) U1 with HASP (3) Bulkhead	5		
< >	CM, Latch, Southco M1, 2" S/S, (1/4" Door) Locking, CN 10-Rated 10lb (self latching) Flush Mount. Non-Locking Attendant seat base door	1		
< >	CM, Latch, Southco M1, 2" S/S, (3/8" Door) Non-Locking, CN 10-Rated 10lb (self latching) Flush Mount. Non-Locking Glove Caddy	1		
	06 - ELECTRICAL GENERAL			
<	CM, 12V Electrical system, RelayPlex system Flash Pattern- Quad Flash 75 - Per KKK	1		
	CAMERAS			
U <	Camera, Patient Compartment and Back Up SR#2240242F Item#1 Camera, Patient Compartment SAP#10495001Hanscom kit HK 7211. Mount monitor to the left of the steering wheel. Bracket Part #10130864 In the module mount the camera on the headliner next to the StreetSide cabinets.Trigger camera display on with Master Switch. #HC IR250 rear back up camera with #HC20M video cable, Mount camera exterior on rear of module, off center toward driver's side. Triggered when units placed in reverse gear. See reference picture on file	1		
	COMMUNICATION			
<	CM, Coax Cable, RG58/U, Each, Terminate: CS Dome #2 to behind pass seat with 6' pigtails S/Side From Dome #4 to behind the drivers seat with 6' pigtails S/Side From Dome #5 to behind the pass seat with 6' pigtails	3		
<	CM, Light, in Circuit Board Area, for Electrical Troubleshooting - with integral switch; wired constant hot.	1		
	POWER SOURCES			
<	CM, Power Source, 12VDC, 20A, Ignition/Shoreline Hot (1) pre-wire coil and tagged in action area	1		

DESCRIPTION	QTY		
(1) pre-wire coil and tagged behind driver's seat. < CM, Power Source, 12 VDC, 20 Amp (+-), Constant Hot Termination: (1) in Action Area (1) in cab console < CM, Power Source, 12 VDC, 30 Amp (+-), Ignition Hot (2) Behind Passenger seat with 6 ft coiled wire < CM, Power Source, 12VDC, 40A, Constant Hot (1) Install a 40Amp Power and ground wired CONSTANT hot to a Buss bar inside the center console (1) Install a 40Amp Power and ground wired IGNITION hot to a Buss bar inside the center console < > CM, Buss Bar Assembly (+/-), 5 Position, (1) Power and (1) Ground Location: Front chassis cab console VOLTMETER < CM, Alarm, Low Voltage, Audio/Visual Light in cab console and Buzzer in cab. BATTERY SYSTEM < CM, Battery Switch, RelayPlex Electronic w/5 min Timer, Ford T3, Gasoline - Activated thru OEM ignition switch, timer function upon ignition "off". - Momentary rocker switch, on driver's side of cab console, to function as timer shutoff and also reactivate timer. - ONLY Module power is turned on/off. - Chassis power is NOT turned off. 12VDC OUTLETS < CM, Power Outlet, Power Point Style, (2), (1) Action Area (1) RF ALS Cabinet on standard 20-amp ignition hot circuit. - (1) outlet in action area - (1) in RF Cabinet "U8", wall #2, upper right < > CM, Power Outlet, Power Point Style, Each Ignition Hot (1) At foot of squad bench just above 110v outlet. Approx 3" over from the edge cabinet C6. (1) in RF Cabinet L8, wall #2, upper right < CM, Power Outlet, Kussmaul, USB Dual Port, 5VDC, 4.8 Amp, switch panel Ignition Hot (1) Located in the cab switch panel passenger side. (1) located top left of console face. (1) located top right of console face. < > CM, Power Outlet, Kussmaul, USB Dual Port, 5VDC, 4.8 Amp, switch panel, Addition	2 2 2 2 1 1 1 2 3 1		

DESCRIPTION	QTY		
Passenger upper grille light will be Phase 2P Drivers upper grille light will be Phase 1P Passenger lower grille light will be Phase 1P Drivers lower grille light will be Phase 2P Curbside Front intersection will be phase 2P Front upper corner will be Phase 1 Rear intersection will be Phase 1 Rear upper corner will be Phase 2 Street side Front intersection will be phase 1P Front upper corner will be Phase 2 Rear intersection will be Phase 2 Rear upper corner will be Phase 1 Rear Street side upper corner will be Phase 1 Center upper light shall be Phase 2 Curbside upper corner will be Phase 1 Street side below upper outer corner will be Phase 2 Curbside below upper outer corner will be Phase 2 NOTE: Hundred series lights must be set to steady burn and flashed thru RelayPlex			
< CM, Brake Override Circuit For rear lights below upper outer corner	1		
WARNING LIGHTS > LED Series - 900 (Flange Separate) < > CM, Light, Whelen 900 LED, Red, Clear Lens, 90RR5SCR, External Flasher MODULE SIDES LIGHTING Street side Body - Upper Forward Street side Body - Upper Rear Curbside Body - Upper Forward Curbside Body - Upper Rear Pri/Sec flashed thru relayplex quad flash 75 MODULE REAR LIGHTING Rear Body - Upper Street side Corner Rear Body - Upper Curbside Corner Pri/Sec flashed thru relayplex quad flash 75 FRONT UPPER BODY LIGHTING Front Body - Upper Curbside Outer Angled portion of Coolbar Front Body - Upper Curbside Inner on Coolbar Front Body - Upper Street side Inner on Coolbar Front Body - Upper Street side Outer Angled portion of Coolbar Pri only flashed thru relayplex quad flash 75 MODULE REAR LIGHTING (2) Rear just below upper outer lights.	12		

DESCRIPTION	QTY		
Pri/Sec flashed thru relayplex quad flash 75 W/Brake override			
< > CM, Light, Whelen 900 LED, Amber, Clear Lens, 90AA5SCR, External Flasher MODULE REAR LIGHTING Rear Body - Upper Center Pri/Sec flashed thru relayplex quad flash 75	1		
< > CM, Light, Whelen 900 LED, Clear, 90CC5SCR, External Flasher FRONT UPPER BODY LIGHTING Front Body - Upper Center on Coolbar Pri Only flashed thru relayplex quad flash 75	1		
CM, Flange, Super 900 LED, #90FLANGC	14		
> LED Series - 700 (Flange Separate)			
< > CM, Light, Whelen 700 LED, Red, Clear Lens, 70R02SCR FRONT UPPER BODY LIGHTING (2) Front Body - Upper Curbside Corner stacked (2) Front Body - Upper Street side Corner stacked Pri/Sec flashed thru relayplex quad flash 75 FRONT FENDER INTERSECTION LIGHTING Front Fender Warning - Intersectors - LH Side Front Fender Warning - Intersectors - RH Side Pri only flashed thru relayplex quad flash 75 REAR WHEEL WELL INTERSECTION LIGHTING Rear wheel well Warning - Intersectors - LH Side Rear wheel well Warning - Intersectors - RH Side Pri/Sec flashed thru relayplex quad flash 75	8		
WHELEN FLANGES 7 SERIES LIGHTS (Flange Separate) < CM, Flange, Whelen, Chrome, 700 Series Light (1) For 7 Series Lights WARNING LIGHTS -WHELEN LIN3 (Flange Separat < > CM, Light, Whelen, LIN3, LED-Red, RSRO2ZCR w/Flg FRONT GRILL LIGHTING Grille - LH Upper Corner Grille - RH Upper Corner Grille - LH Lower Corner Grille - RH LowerCorner Pri only flashed thru relayplex quad flash 75 X-pattern Flash CM, Flange, Whelen, Chrome, For LIN3, Each EXTERIOR AUTOMOTIVE LIGHTING < CM, Taillight Pkg, Whelen, LED Stop/Tail, Turn & LED Backup, w/WC logo - Brake- Steady Burn - Turn Arrow – sequential arrow - 700 LED Backup Clear lens over all three lights ICC/MARKER LIGHTS < CM, Light, Red, 2", Marker, LED, Each in bumper	8		

DESCRIPTION		QTY		
<	CM, Clearance Lights, Red, LED (3) On rear as clearance lights.	3		
<	CM, Light, Clearance, Amber LED (3) On Front of module as clearance lights.	3		
<	CM, Corner Cap Lts, Multi, LED, (2) Amber (2) Red w/Flashers - High intensity flashers;Primary/Secondary- As marker lights with headlights	1		
FLOOD AND LOAD SYSTEMS				
<	CM, Light, LED, Whelen, Clear, #9SC0ENZR, 24 LED, (1) w/ Chrome Flange (2) each side as scene lights (2) on rear as load lights	6		
<	CM, Scene Lights, C/S, Activated with C/S Door Master Hot.	1		
11 - INTERIOR LIGHTING				
<	CM, Dome Lights, LED, Whelen, White Flange,(3)S/S,(3)C/S, CM+ Three (3) street side in liner and three (3) curbside in liner equally spaced Each side controlled by separate switch in action area standard. High/Off/Low NOTE: NO VISABLE FASTENERS OR HOLES.	1		
<	CM, Timer, Momentary Switch, 15 Minute, Constant Hot Mount switch on C/S wall at the head of the squad bench in the standard location. Switch to allow activation and also deactivation. Wire to street side dome lights in liner on high.	1		
	WC, No Lighting Recessed into Trough Cover	1		
SPOTLIGHTS / HANDHELD LIGHTS				
	CM, Handheld Spotlight, Novatech, Nighthawk 2000, 100,000 CP	1		
ATTENDANT LIGHT				
	CM, Light, Intertek ZY-PIR38 12v, 15" LED, In A/A	1		
SHORELINE INLET				
<	CM, Super Auto Eject, 20A, White Cover above comp "#2"	1		
OUTLETS - 125VAC				
<	CM, Outlets, 125 VAC, Duplex, (1) Action Wall, (1) Right Front Cabinet - (1) outlet in action area - (1) outlet in the RF Cabinet "U8", wall #2, upper right.	1		
< >	CM, Outlet, 125 VAC, Duplex, Additional, Each (1) Interior CS above foot end of squad bench mounted approx. 14" up and over 3" from cabinet C6. (1) telemetry area, wall 2 near wall 1, mid height	2		

DESCRIPTION	QTY		
BLOCKHEATERS			
< Block Heater - With OEM Plug This option does not include a switch. (STANDARD).	1		
INVERTER - 125VAC			
< > CM, Inverter/Charger, Vanner LifeSine Mounted on ceiling of comp#2	1		
AUXILIARY ENVIRONMENTAL SYSTEMS			
< CM, Exhaust Fan, Single 12V Blower with "clamshell" vent on exterior forward of #4	1		
CM, Generation I, Steel Cool Bar cover	1		
CITIMEDIC BRUSHLESS HVAC SYSTEM			
< > CM, Heat/AC, F3, Combo, Brushless, w/Coolbar with thermostat in action area.	1		
12vdc External Condenser, in Coolbar mounted on front of module. Ford White: PPG Code - FBCH978045			
CM, Thermostat, Master Control Digital CM5000, Brushless	1		
Cover, Cool Bar, (5) 900 series lights, LED Lights	1		
CM, Air Conditioning Face Plate, Brushed Stainless	1		
Steel with WC Logo			
> WC, Heat/AC Located RF corner, over ALS cabinet.	1		
COT MOUNTING PROVISIONS			
Safety Hooks			
< CM, Cot Mount, Stryker, Rear Safety Hook Installed Ship Loose	1		
Cot Mounts			
< > CM, Stryker Performance/Power Load, Add Floor Structure Plates & Wiring for Futu Additional floor structure for future installation of a Stryker Performance Load w/ inductive charging System.	1		
< CM, Cut Floor and Install Stryker Floor Plate, 6390-700-001A, for Performance For Performance Load Cot mounts.	1		
Note: Stryker Deutsch connection to be coiled up on the interior of the module under attendant seat base			
CM, Power source for Induction Charging, 12V, 10 Amp	1		
constant hot			
Center Mount	1		
OXYGEN AND AIR SYSTEMS			
< CM, O2 Cylinder Wrench, Tethered in oxygen compartment.	1		
< CM, Rack, Multiversal, Zico #QR-MV, W/ Straps Set up for M cylinder size	1		
CM, Track, Unistrut for Oxygen Rack	1		
CM, Manual, O2 System	1		
< CM, O2 Regulator, Preset 50PSI Ship Loose	1		

DESCRIPTION		QTY		
<	CM, O2 System, Ohio Style, (2 AA, 1 Vac Diss, 1 Liner, 1 C/S) Ohio style outlets (2) oxygen outlets in action area (1) vacuum Diss Outlet in action area (1) oxygen outlet in liner at the chest of cot (1) oxygen outlet curbside wall at head of squad bench	1		
	CM, Lexan Flap, w/Hinge	1		
SUCTION SYSTEM				
<	CM, Suction Pump, SSCOR 90206 mounted in compartment "2"	1		
< >	CM, Suction Holder, SSCOR 23002 with w/Canister Clip & Regulator See oxygen system for type of fitting used for container	1		
< >	WC, Suction Outlet and Container located in Action area recess Suction container in recess in cabinet recess in wall below action area countertop.	1		
MISC MEDICAL				
<	CM, Fire Extinguisher, Additional, 5 LB. ABC, Ship Loose, Each HD Amerex Bracket #861H with Amerex 5LB fire extinguisher.	1		
PAINT AND FINISH				
	WC, Wheeled Coach Paint Process	1		
< >	RM & CM, Module Paint, Single Color, OEM White Ford White: PPG Code - FBCH978045	1		
< >	RM & CM, Cab Paint - Single Color, OEM White Ford White: PPG Code - FBCH978045	1		
PAINT STRIPING DESIGN				
	Paint Belt, None	1		
GRAPHICS AND LETTERING DECALS AND NOMENCLATURE				
<	CM, Decal, Roof Star, Installed 32" roof star of Life	1		
SHIP LOOSE ITEMS				
	CM, Bracket, Spare Tire Mounting, Ship Loose	1		
<	Indemnification Statement The purchaser agrees to defend, indemnify and hold Rev Ambulance Group harmless from any claims, costs (including actual attorneys' fees), damages and liabilities caused in whole or in part by any alteration or modification of, or changes or additions to the purchased products OR use of product for purposes it was not designed or intended for.	1		